



+ CONNECTORS  
HOUSINGS



✓ Active

TE CONNECTIVITY (TE)  
**MOD 4 REC.HSG 1X16P**  
[AMPMODU](#) | [AMPMODU IV/V](#)

1-925369-6  
TE Internal Number: 1-925369-6

[EU RoHS Compliant](#)  
[EU ELV Compliant](#)

**Centerline (mm)** 2.54  
**Termination Method to Wire/Cable** Crimp  
**Centerline (Pitch) (in)** .1  
**Number of Rows** 1  
**Row-to-Row Spacing** 2.54 mm [ .1 in ]

 **PRODUCT DRAWING**  
English

 **3D PDF**

DOCUMENTATION

Product Drawings

**AMPMODU IV GEHAEUSE, EINREIHIG**  
PDF  
English

CAD Files

**Customer View Model**  
3D\_IGS.ZIP  
English

**Customer View Model**  
3D\_STP.ZIP  
English

**Customer View Model**

2D\_DXF.ZIP

English

3D PDF

PDF

3D

Product Specifications

Product Specification

AMPMODU Mod 1/2 Wire To Board Standard Pressure Contact Interconnection System

PDF

English

Agency Approvals

Agency Approval Document

AMPMODU CONNECTOR REPORT (GERMANY)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Row-to-Row Spacing 2.54 mm [ .1 in ]
- Terminates To Printed Circuit Board
- Glow Wire Rating Standard Part - Not Glow Wire
- Strain Relief With
- Connector Type Housing
- Connector Style Receptacle
- Product Type Connector

Configuration Features

- Number of Rows 1
- Number of Positions 16

Electrical Characteristics

- Operating Voltage 250 VAC

Body Features

- Color Green

Contact Features

- Contact Layout Inline
- Contact Type Socket

Termination Features

Termination Method to Wire/Cable   Crimp

Mechanical Attachment

Mating Retention   With

Mating Retention Type   Lock

Mating Connector Lock   Without

Mating Alignment   Without

Mating Alignment Type   Polarization

Housing Features

Centerline (mm)   2.54

Centerline (Pitch) (in)   .1

Housing Material   PA 6.6

Housing Color   Green

Housing Configuration   Both Ends Closed

Dimensions

Length (in)   4.99

Height (in)   .11

Usage Conditions

Operating Temperature Range (°C)   -65 – 105

Operation/Application

For Use With   AMPMODU Mod II .025 inch Headers

Industry Standards

UL Flammability Rating   UL 94V-0

Packaging Features

Packaging Method   Carton

Packaging Quantity   1000

Statement of Compliance

Statement of Compliance

PDF