




Part Number : 1461530250
Product Description : Wi-Fi 6E Flex Cabled
Balanced Antenna, 9.00mm Width, 250.00mm
Cable Length, Compatible with U.FL / I-PEX
MHF Connectors
Series Number : 146153
Status : New Business Not Supported
Product Category : Antennas



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
Category	Antennas
Series	146153
Description	Wi-Fi 6E Flex Cabled Balanced Antenna, 9.00mm Width, 250.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Family	Internet of Things (IoT) Antennas: Wi-Fi, Bluetooth, Zigbee
Product Name	2.4/5GHz Balanced Flex Antenna
Protocol	BLE, BT, Thread, Wi-Fi, Wireless Hart, Zigbee
Type	Internal, Wi-Fi Antenna
UPC	889056310840

Electrical

Band#1 F_End (MHz)	2483.5
Band#1 F_Start (MHz)	2400
Band#2 F_End (MHz)	5930
Band#2 F_Start (MHz)	4900
Electrical Connectivity	Cable
Peak Gain (dBi)	2.4 @ 2.4 GHz, 3.2 @ 5 GHz
Return Loss - S11 (dB)	< -10
Total Efficiency	>63% @ 5 GHz, >66% @ 2.4 GHz

Physical

Cable Length	250.00mm
Length	34.90mm
Mounting Style	Adhesive
Net Weight	1.024/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm

Width	9.00mm
-------	--------

This document was generated on Dec 11, 2023