

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1554116001

Status:

Active

Overview:

Description:

Flamar Ethernet 5e Network Cable, PVC Jacket, Braided Shielding Overall, 4 Circuits, 2x(2x0.14mm²) / 2x(2x26 AWG), 6.50mm (.256") Diameter, 300.0m (984.25') Length, Teal

Agency Certification	
UL	E172949
General	
Product Family	Cable
Series	155411
Comments	3 reels of 100.0m each
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	flamar_standard_industrial_cables
Product Name	Flamar, Network
Protocol	EtherNet 5e
Taxonomy	Industrial Cable
UPC	889056463393
Physical	
Bending Radius - Minimum	> 15xOD
Cable Length	300.0m
Circuits (Loaded)	4
Color - Cable Jacket	Teal
Insulation	PE
Material - Outer Jacket	PVC
Net Weight	0.054/kg
Outer Jacket Diameter	6.50mm
Packaging Type	Reel
Temperature Range - Operating	+5° to +60°C
Wire Size AWG	26
Wire Size mm²	0.14
Wire/Cable Type	UL AWM 2464 / CSA
Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	300V
Material Info	
Engineering Number	3X100M
Reference - Drawing Numbers	
Product Specification	1554116001-P1E

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

155411 Series

Use With

Micro-Change (M12) [130047](#) , [120100](#) ,
[130034](#) , [120071](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION