

# CRYSTAL TEST & BURN IN SOCKET

AXS-4918-02-11

Precision test socket for 4.9X1.8mm,  
2 pad crystal packages.



**RoHS**  
Compliant




## FEATURES:

- Accurate and reliable testing of frequency control devices
- Contact force ideal for avoiding measurement error
- Highest quality socket available
- Clam shell design for easy open and close
- Reliable gold plated POGO pins
- Suitable for high temperature burn-in test
- Operating Temperature: -30 ~ +150°C


## APPLICATIONS:

- Design stage component engineering evaluation
- Supplier comparison tests
- High temperature burn-in board testing
- Prototyping


## SIDE VIEW (OPEN):




## POCKET TOP VIEW:




## PIN DIMENSIONS:



## END VIEW:



## SUITABLE CRYSTAL PACKAGE DIMENSIONS:



\*Typical 32.768kHz package

Dimensions: mm

## ORDERING INFORMATION:

When ordering, please refer to part number

# AXS-4918-02-11

## RECOMMENDED FOR USE WITH DEVICE PACKAGE DIMENSIONS:

**4.9 x 1.8 x 0.9mm**

## COMPATIBLE ABRACON SURFACE MOUNT CRYSTAL:

### ABS10 Series

(for a pdf download go to [www.abracon.com/Resonators/ABS10.pdf](http://www.abracon.com/Resonators/ABS10.pdf))

\* ABRACON test and burn in sockets are compatible with all industry standard frequency control packages.

ABRACON IS  
ISO 9001 / QS 9000  
CERTIFIED



**ABRACON**  
CORPORATION

Visit [www.abracon.com](http://www.abracon.com) for Terms & Conditions of Sale **Revised: 07.10.09**

30332 Esperanza, Rancho Santa Margarita, California 92688

tel 949-546-8000 | fax 949-546-8001 | [www.abracon.com](http://www.abracon.com)