



0 Reviews



0 Reviews

Need Help?

SHOP PRODUCTS

All

Search by keyword, connector, or sku



LIVE CHAT & HELP

Browse All Products | Fiber Optic Cables | 9/125 Duplex Single-Mode Fiber Optic OS2 | 9/125 Duplex Single-Mode Plenum Fiber

Loading...

15m SC-ST 9/125 OS2 Duplex Single-Mode Fiber Optic Cable - Plenum CMP-Rated - Yellow

9/125 micron cable for gigabit ethernet applications; OFNP plenum-rated for in-wall use without conduit



0 Reviews

Roll over image to zoom in

Product #: 34522

Connector 1: (1) SC Male

Connector 2: (1) ST Male

Lengths:

49.2ft

3.3ft

6.6ft

9.8ft

13.1ft

+ show all lengths

Request availability



Add



print share chat

Product Info

Customer Reviews

Questions & Answers

Distributors

More Choices

Description

Certifications

Specs

Product Description

Cost-effective solution that provides high bandwidth and transmission rates over longer distances. With SC to ST termination, this high quality fiber optic patch cable is specifically designed for gigabit ethernet applications. The plenum rating provides the fire protection required to run this cable within walls and air plenums without using conduit. The patented injection molding process provides each connection greater durability in resisting pulls, strains and impacts from cabling installs.

Each cable is 100% optically inspected and tested for insertion loss before you receive it. A pull-proof jacket design surrounds the popular 9/125 Single-mode fiber, immune to electrical interference.

WARNING: Cancer and Reproductive Harm www.P65Warnings.ca.gov

Product Certifications



Product Specifications

Color:

Yellow

Length :	15.00 Meter
UPC :	757120345220
Warranty :	Lifetime
Vendor :	C2G
Weight :	0.498 LB

- SC Connector Dimensions: 10.6mm Height x 26mm Width x 58mm Depth (with installed duplex clip)
- ST Connector Dimensions: 9.8mm Height x 19.6mm Width x 59mm Depth
- Maximum Connector Loss: 0.50 dB
- Typical Connector Loss: 0.30 dB
- Typical Return Loss: -55 dB
- Buffer Material: PVC
- Buffer OD: 900 µm
- Jacket Material: Plenum (OFNP-rated)
- Jacket OD: 2.8 mm
- Installation Tensile Load: 100 N (445 lbs)
- Long-Term Tensile Load: 50 N (222 lbs)
- Maximum Tensile Load: 100 N/cm
- Installation (Loaded) Minimum Bend Radius: 5.0cm (1.97in)
- Long-Term (Unloaded) Minimum Bend Radius: 3.0cm (1.2in)
- Crush Resistance: 750 N/cm
- Impact Resistance: 1,000 cycles
- Flex Resistance: 5,000 cycles
- Attenuation at 1550 nm: 0.25 dB/km
- Attenuation at 1310 nm: 0.35 dB/km
- Operating Temperature: -20°C to +70°C

Please Note: Attenuation testing performed in accordance with EIA/TIA-455-171A.

Recently Viewed...



Info

- About Us
- Order History
- Where To Buy
- More ▾

Service

- Contact Us
- OEM Solutions
- Tech Support
- More ▾

Resources

- Connector Guides
- ConnectXpress
- Drivers & Manuals
- More ▾

Have A Question?

- Get help with [Chat](#)
- Call C2G **800.506.9607**



United States | Europe +

Copyright © 2019 C2G. All Rights Reserved

