Pushing Performance
Since 1945

Han 6EMC/B-HSE-M25 (HT)



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 806 0546
Specification	Han 6EMC/B-HSE-M25 (HT)
HARTING eCatalogue	https://harting.com/19628060546

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® EMC/B Han® High Temp
Type of hood/housing	Hood
Type	High construction

Version

Size	6 B
Version	Side entry
Number of cable entries	1
Cable entry	1x M25
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C -40 ... +200 °C With Han® High Temp components
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP66
Type rating acc. to UL 50 / UL 50E	4 12

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
PFAS	No
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE UKCA DNV GL

Commercial data

Packaging size	1
Net weight	117 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140132597
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.