



UNIT : mm



- Electronic Test:
- 1.100% Test,(Open,Short,Miss Wire)
 - 2.Contact Resistance:2 ohm max.
 - 3.Insulation Resistance:5M ohm min.
 - 4.Hi-Pot:100V DC/10ms



PIN ASSIGNMENT

P1	P2
1 BLACK	1
2 GREY	2
3 YELLOW	3
4 PURPLE	4
5 ORANGE	5
6 RED	6
7 BROWN	7
8 GREEN	8
9 BLUE	9
SHELL D.W	SHELL

⑧	TUBE	2	HEAT SHRINK TUBE BLACK OD1.5*L15MM
⑦	PE BAG	1/10	CLEAR SIZE:280*330*0.05mm PRINT BLACK"MADE IN CHINA"+*10PCS" 及印生产日期,有透气孔.
⑥	TIE	1	WHITE L=100mm
⑤	PE BAG	1	CLEAR SIZE:130*230*0.05mm PRINT BLACK"MADE IN CHINA"+*1PC 及印生产日期,有透气孔.
④	OUT JACKET	10.7/9	BEIGE(V-29) 30P PVC(LS-003)
③	SCREW	4	SCREW:#4-40UNC L47mm,NICKEL PLATED
②	OUT JACKET	43.5/5g	BEIGE(V-29) 40P PVC(MOULD NO:WM-113)
①	IN JACKET	8g	CLEAR LDPE(MOULD NO:NM-049)
⑦	CONN	2	DB 9PIN FEMALE PIN G/F SHELL-NICKEL SOLDER TYPE INSULATION COLOR BLUE
⑥	CABLE	1	NOUL 30AWG(7/0.10)*9C+D+W+AL/M+JACKET COROL:BEIGE(V-29) OD:5.0mm. L2000±10mm.

SPECIFICATION

CnC Tech, LLC
Industrial Cable and Connector Technology

DRAWN BY	ZHONGHS	DRAWING NO.	
CHECKED BY		CUSTOMER	
APPROVAL BY		ITEM NO.	710-10025-00200
DECIDE BY		DATE	2012-02-06
VERSIONS/EDITION	A/0	PROJECTION	