
molex



Part Number : 1731070538
Product Description : FCT Mixed Layout D-Sub Connector, Male, Right-Angle, PCB Through Hole, Gold Plating, Tin-plated Shell with Dimples, 14.50mm Riveted Metal Bracket and Bushing, 5 Circuits Max, 1 High Power Contact Loaded, Green Insulator
Series Number : 173107
Status : Active
Product Category : D-Sub Connectors
Engineering Part Number : FM5W1P-1177

Documents and Resources

Drawings

1731070538_sd.pdf

Symbol and Footprint (Multi-Format)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Connectors
Series	173107
Description	FCT Mixed Layout D-Sub Connector, Male, Right-Angle, PCB Through Hole, Gold Plating, Tin-plated Shell with Dimples, 14.50mm Riveted Metal Bracket and Bushing, 5 Circuits Max, 1 High Power Contact Loaded, Green Insulator
IP Rating	IP20
Magnetic	Yes
Product Name	FCT Products
Type	Mixed Layout
UPC	191128457477

Electrical

Current - Maximum per Contact	20.0A
Shielded	Yes

Physical

Circuits (Loaded)	1
Circuits (maximum)	5
Color - Resin	Green
Durability (mating cycles min)	500
Gender	Male

Downloaded from Arrow.com.

Material - Contact	Copper Alloy
Material - Resin	Polybutylene Terephthalate (PBT)
Material - Shell	Steel
Net Weight	9.400/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Carton
Panel Mount	Rear
Panel Mount Method	Thread-In
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	6.80mm
Pitch - Mating Interface	2.84mm
Pitch - Termination Interface	2.54mm
Plating - Contact	Gold over Nickel
Plating min - Mating	0.800µm
Plating min - Termination	5.000µm
Plating - Shell	Tin
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Shell Size	1
Temperature Range - Operating	-55° to +130°C
Termination Style	Through Hole
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	FCT Mixed Layout D-Sub, Size 1, 5W1, Socket

Downloaded from Arrow.com.

This document was generated on May 20, 2026

Downloaded from Arrow.com.