



N = Number of contacts

#### DIMENSION

A	NX3.5
B	(N-1)X3.5

Poles	Tolerance
2P-8P	±0.10
9P-16P	±0.20
17P-24P	±0.30

SIGN	DATE	DESCRIPTION	APPROVER
△	8/07'06	Added VDE standard	梁仁松
△	2008.12.02	With flange screw changed from "-solt type to "+/-solt type	Jacke
△	2008.12.02	The temperature changed from -30°C,+105°C to -40°C,+115°C	Jacke
△	2008.12.02	The dimension design changed from 19.1mm to 19.3mm	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

#### Material

- Item① Clamp: Brass(CuZn),Nickel plated
  - Item② Terminal screw: Steel Zinc plating "- slot type
  - Item③ Female contact: PhBz, Tin plated
  - Item④ Terminal (housing): Thermoplastic (UL94V-0)
  - Item⑤ Terminal (cover): Thermoplastic (UL94V-0)
  - Item⑥ With flange screw: Steel M2.5 Zinc plating "+/- slot type
- Electrical cULus/VDE

- Voltage rating: 300VAC/300VAC
- Current rating: 8A/10A
- Wire range: 1.5mm<sup>2</sup>
- Solid wire(AWG): 16-28
- Stranded wire(AWG): 16-28
- Torque: 1.7Lb-In./0.2Nm
- Screw: M2
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV
- △ Operating temperature: -40°C to +115°C
- △ Safety approval: cULus VDE

#### TS xx 1 1 x D xxxx G

No. OF POLES	Color	RoHS pb<40,000ppm
02: 2 POLES	0 Black (RAL9005)	0000 Standard @ Logo
:	2 Red (RAL3001/D)	000A Standard ANY Logo
:	3 Orange(RAL2011/P)	Any special item by
24: 24 POLES	4 Yellow(RAL1018/A)	customer request,
	5 Green(RAL6018/T)	please contact sales
	6 Blue (RAL5015/A)	department.
	8 Grey(RAL7035/D)	

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TS-3.5mm Series With flange (for latch on back side)			
PART NO.	TSxx11xDxxxxG			DWG NO.	8TS0204
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Jacke	Jacke		X. ±0.50
		2008.12.10	2008.12.10		X.X ±0.30
					X.XX ±0.10
					X° ±1°
SHEET: 01/01		UNIT: mm		SCALE: NONE	
				REV.: E	