

- ⌚ **Height:** 1.5mm Max
- ⌚ **Footprint:** 3.8mm x 3.4mm Max
- ⌚ **Current Rating:** up to 7.0A
- ⌚ **Inductance Range:** 0.22uH to 10.0uH
- ⌚ High current, low DCR, and high efficiency
- ⌚ High reliability
- ⌚ 30 Vdc Voltage Rating between terminals
- ⌚ Minimized acoustic noise and minimized leakage flux noise

Electrical Specifications @ 25°C - Operating Temperature -55°C to +125°C


Commercial ^{5,6}	Automotive ^{5,6}	Inductance 100KHz, 1.0V	Rated Current	DC Resistance		Saturation Current
				TYP.	MAX.	
		uH±20%	A	mΩ	mΩ	A
PA4547.221NLT		0.22	7.00	14	17	10.8
PA4547.471NLT	PM4547.471NLT	0.47	5.50	23.3	28	8.0
PA4547.561NLT	PM4547.561NLT	0.56	5.00	28	33	7.2
PA4547.681NLT	PM4547.681NLT	0.68	4.50	34	42	6.5
PA4547.102NLT	PM4547.102NLT	1.00	3.60	41	50	5.8
PA4547.152NLT	PM4547.152NLT	1.50	3.40	64	77	4.0
PA4547.222NLT	PM4547.222NLT	2.20	3.20	82	98	3.8
PA4547.332NLT	PM4547.332NLT	3.30	2.50	170	205	3.2
PA4547.472NLT	PM4547.472NLT	4.70	1.90	220	264	2.8
PA4547.562NLT	PM4547.562NLT	5.60	1.70	265	318	2.3
PA4547.682NLT	PM4547.682NLT	6.80	1.50	290	348	2.0
PA4547.822NLT	PM4547.822NLT	8.20	1.30	390	468	1.8
PA4547.103NLT	PM4547.103NLT	10.00	1.20	435	522	1.6

Notes:


- Actual temperature of the component during system operation (ambient plus temperature rise) must be within the standard operating range.
- The saturation current is the current at which the initial inductance drops approximately 30% at the stated ambient temperature. This current is determined by placing the component in the specified ambient environment and applying a short duration pulse current (to eliminate self-heating effect) to the component.
- The rated current is the DC current required to raise the component temperature by approximately 40 °C. Take note that the components' performance varies depending on the system condition. It is suggested that the component be tested at the system level, to verify the temperature rise of the component during system operation.
- The part temperature (ambient+temp rise) should not exceed 125 °C under worst case operating conditions. Circuit design, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.
- Parts shown in bold are standard catalog parts and are available through sample stock and distribution. Parts in lighter font are available but are not necessarily held in sample stock or distribution **and lead times may be longer**. Please contact Pulse for availability.
- The PA4547.XXXNLT and PM4547.XXXNLT are both AEC-Q200 qualified. The PM4547.XXXNLT part numbers are also IATF16949 certified. The mechanical dimensions are 100% tested in production but do not necessarily meet a product capability index (Cpk) 1.33 and therefore the PM4547.XXXNLT may not strictly conform to PPAP.

Mechanical

PA4547/PM4547



FINAL LAYOUT




SUGGESTED PAD LAYOUT

Series	A	B	C	D	E	L	G	H
PA4547/PM4547	3.5±0.3	3.2±0.2	1.3±0.2	0.7±0.2	1.2±0.2	4.1	1.9	1.45

All Dimensions in mm.

TAPE & REEL INFO



SURFACE MOUNTING TYPE, REEL/TAPE LIST						
	REEL SIZE (mm)		TAPE SIZE (mm)			QTY
	A	G	P ₁	W	K ₀	
PA4547/PM4547	Ø330	12.4	8	12	1.8	3000

For More Information:

Americas - prodinfo_power_americas@yageo.com | Europe - prodinfo_power_emea@yageo.com | Asia - prodinfo_power_asia@yageo.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2026. Pulse Electronics, Inc. All rights reserved.