






APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	08/02/01	
A		UPDATE DRAWING	5/17/18	AY/TW



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:
 Material: PBT, Glass Fiber, rated UL 94V-0
 Insulator color: Black
 Contacts: Phosphor Bronze
 Plating:
 Round over Nickel underplate overall
 Flat contact
 Gold over Nickel underplate on contact area,
 Tin over Nickel underplate on solder tails
 Electrical:
 Voltage Rating: 150 VAC max
 Current rating: 1.5 Amps max
 Contact Resistance: 20 mohms max.
 Insulation resistance: 500 Mohms min @500 VDC
 Dielectric withstanding voltage: 1000 Vrms for 1 minut
 Operating temperature: -40°C to +85°C
 Environmental:
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]	
TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLDS
.X ± .10	± .10
.XX ± .020	± .015
.XXX ± .015	± .010
ØXXX	ØXXX
APPROVALS	DATE
DRAWN	SLS
CHECKED	
APPROVED	

ADAM TECH 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Intercconnects Fax: 908-687-5710

**MODULAR TELEPHONE JACK, 6P4C
 RIGHT ANGLE, PCB**

SIZE: X PART NO.: MTJ-64FX1
 REF: S00065T SCALE: NTS SHEET 1 OF 1