








P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	14NOV2019	DW	CW
	A1	ECR-20-008707	17JUN2020	DW	CW
	B	ECR-21-111798	07OCT2021	WQR	CW



- NOTES:
- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: POWER: 830V; SIGNAL: 830V
RATED CURRENT: POWER: 40A; SIGNAL: 10A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: POWER: 8KV; SIGNAL: 8KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
TEMPERATURE RANGE: $-40\sim+125^{\circ}C$
WIRE RANGE: POWER: $1\sim6\text{ mm}^2$ (18~10 AWG)
SIGNAL: $0.14\sim2.5\text{ mm}^2$ (26~14 AWG)
CONTACT TYPE: CRIMP CONTACT
 - CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:
T20400X20XX000 FOR POWER;
T20200X20XX000 FOR SIGNAL)

- 注释:
- 技术参数:
绝缘材料: PC
额定电压: 电源: 830V; 信号: 830V
额定电流: 电源: 40A; 信号: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 电源: 8KV; 信号: 8KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
温度范围: $-40\sim+125^{\circ}C$
接线范围: 电源: $1\sim6\text{ mm}^2$ (18~10 AWG)
信号: $0.14\sim2.5\text{ mm}^2$ (26~14 AWG)
接线类型: 冷压接
 - 端子需要单独订购.
(订货号参考图面: 电源端子: T20400X20XX000; 信号端子: T20200X20XX000)

T2111342201-000	HMN-3/4-F	HMN-3/4 FEMALE MODULE INSERT HMN-3/4 模块母插
PART NUMBER 料 号	PART DESCRIPTION 描 述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11JUL2019 DAVID WANG	 TE Connectivity		
		CHK 11JUL2019 GINO YAO			
DIMENSIONS: mm 		APVD 11JUL2019 CHRIS WANG	NAME HMN-3/4-F		
		PRODUCT SPEC 108-137418			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		APPLICATION SPEC 114-137418	SIZE CAGE CODE DRAWING NO RESTRICTED TO		
		WEIGHT -	A300779 T2111342201000 -		
MATERIAL -		CUSTOMER DRAWING		SCALE 3:2	SHEET 1 OF 1
				REV B	