


ZB 5,LGS:L1-N,PE - Zack marker strip



1050415

<https://www.phoenixcontact.com/us/products/1050415>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, white, labeled, horizontal: L1, L2, L3, N, PE, L1, L2, L3, N, PE, mounting type: latching, for terminal block width: 5.2 mm, Number of individual labels: 10, text field height: 10.5 mm, text field width: 5.15 mm

Your advantages

- Other pitches available on request
- The multi-section marking strips are easy to fit and can be easily separated if required
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves
- Unmarked marking strips can be custom-labeled with a plotter or by hand

Commercial data

Item number	1050415
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2122
GTIN	4017918015701
Weight per piece (including packing)	1.32 g
Weight per piece (excluding packing)	1.066 g
Customs tariff number	49119900
Country of origin	DE

ZB 5,LGS:L1-N,PE - Zack marker strip



1050415

<https://www.phoenixcontact.com/us/products/1050415>

Technical data

Product properties

Product type	Labeled terminal marker
Pitch	5.2 mm

Marking

Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10
Printing direction	horizontal
Printing	L1, L2, L3, N, PE, L1, L2, L3, N, PE

Mounting

Mounting type	latching
---------------	----------

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Specification	IEC 60068-2-2:2007-07
Result	Test passed
Procedure	Test Bb
Duration	96 h
Temperature for testing	120 °C

ZB 5,LGS:L1-N,PE - Zack marker strip



1050415

<https://www.phoenixcontact.com/us/products/1050415>

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Dimensions

Width	5.15 mm
Height	10.5 mm
Depth	4.2 mm
Pitch	5.2 mm

Text field

Text field width	5.15 mm
Text field height	10.5 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Notes

General	10 identically marked strips make up one packing unit (PU).
---------	---

Drawings

Schematic diagram



ZB 5,LGS:L1-N,PE - Zack marker strip



1050415

<https://www.phoenixcontact.com/us/products/1050415>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZB 5,LGS:L1-N,PE - Zack marker strip



1050415

<https://www.phoenixcontact.com/us/products/1050415>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.01 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com