F-Series




The F-Series toggle switches are AC rated up to 20 amps, single pole, with a slow-make, slow-break contact mechanism. These switches are available in a wide range of ratings, circuits, terminations and bushing/toggle configurations.


Specifications

- Certifications*: UL, CSA
- Dielectric Strength: 1,000V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Phenolic
- Actuator Material: Brass/Nickel Plate
- Bushing Material: Brass/Nickel Plate

* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]





2F A 5 3 - 73 /TABS

SERIES

2F	SINGLE POLE
6F	SINGLE POLE MOMENTARY

CIRCUIT

A	ON-NONE-OFF
B	ON-NONE-ON
C	ON-OFF-ON

RATING[1]

5	10A 250VAC 15A 125VAC 3/4HP 120-240VAC
6	3A 250VAC 6A 125VAC 1/4HP 120-240VAC

TERMINATION/FUNCTION[2]

FUNCTION	SOLDER LUG	.250TAB (QC)	SCREW TERM.	WIRE LEAD
ON-NONE-OFF	**3**	**3/TABS**	**4**	**1**
(ON)-NONE-OFF	**3**	**3/TABS**	**4**	**1**
ON-NONE-(OFF)	**7**	**7/TABS**	**8**	**6**
ON-NONE-ON	**3**	**3/TABS**	**4**	**1**
ON-NONE-(ON)	**3**	**3/TABS**	**4**	**1**
ON-OFF-ON	**3**	**3/TABS**	**4**	**1**
(ON)-OFF-(ON)	**3**	**3/TABS**	**4**	**1**
ON-OFF-(ON)	**7**	**7/TABS**	**8**	**6**

TOGGLE STYLE

	TOGGLE LENGTH	BUSHING LENGTH	SUFFIX NO.	NEOPRENE SEAL
BAT	.406	.343	**52**	**57**
	.562	.465	**63**	**68**
	.687	.465	**73**	**78**
	1.00	.343	**A2**	**A7**
	2.00	.465	**E3**	**E8**
BALL	.500	.343	**22**	**---**





NOTES:
Shading indicates standard configurations.
For bushing accessories, see pages 69 and 70.
1 Additional ratings to 20A available. Consult factory.
2 For .187TAB (QC) type terminal use solder lug function selection codes. Add the suffix /.187TABS. (ex.) 2FA53-73/.187TABS

Downloaded from Arrow.com.