



Part Number : [351800600](#)

Product Description : VersaBlade Multi-Module
2-2-2 Hybrid Receptacle Housing, with Mounting Ears,
6 Circuits, Natural

Series Number : 35180

Status : Active

Product Category : Connector Housings



Documents and Resources

Drawings

[351800600 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[351500000AS ENG-000.pdf](#)

[351500000AS KOR-000.pdf](#)


[PK-35180-001-001.pdf](#)

[351800400-001.pdf](#)

[351800600-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	35180
Description	VersaBlade Multi-Module 2-2-2 Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Natural
Application	Power, Wire-to-Wire
Product Name	VersaBlade
UPC	800754249812

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	6
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No

Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	8.066/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	8.00mm, 8.50mm
Pitch - Termination Interface	8.00mm, 8.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Type A, Natural	<u>351810200</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Type B, Natural	<u>351810210</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Type B, Blue	<u>351810214</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Type C, Natural	<u>351810220</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type A, Natural	<u>359650200</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type A, Blue	<u>359650204</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type B, Natural	<u>359650210</u>
VersaBlade Multi-Module Hybrid	<u>359650214</u>

Plug Housing, 2 Circuits, Positive Lock, Type B, Blue	
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type C, Natural	<u>359650220</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type A, Natural, Glow-Wire Capable	<u>359659200</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type A, Yellow, Glow-Wire Capable	<u>359659203</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type B, Natural, Glow-Wire Capable	<u>359659210</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type B, Yellow, Glow-Wire Capable	<u>359659213</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type C, Natural, Glow-Wire Capable	<u>359659220</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type C, Yellow, Glow-Wire Capable	<u>359659223</u>

Use with Part(s)

Description	Part Number
VersaBlade Terminal Position Assurance (TPA) Retainer, 8.50mm Pitch, 3 Circuits, Natural	<u>351820390</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 8.50mm Pitch, 3 Circuits, Red	<u>351820392</u>
VersaBlade Male Crimp Terminal, 24-22 AWG, Type C	<u>2270288400</u>
VersaBlade Male Crimp Terminals	<u>35745</u>

VersaBlade Female Crimp Terminals	<u>35746</u>
VersaBlade Male Crimp Terminals	<u>35747</u>

This document was generated on May 08, 2026