# Datasheet for part number TNM7S14-0304S1L

| Our Catalog Part Number: TNM7S14-0304S1L |
|---|
| Our Global Manufacturing Part Number: 192993-0700 |
| Brand: Cannon Product Category: Trident Product Line: Trident Series: TNM |

| Product Datasheet | |
|---|---|
| Series | Trident Neptune Metal |
| Connector Type | Receptacle for Jam Nut Mounting |
| Environmental Sealing | IP67 |
| Sealing Methode | Sealing Grommet and Gland Nut |
| Shell Size | 14 |
| Contact Quantity | 7 |
| Power Contacts | 3 |
| Signal Contacts | 4 |
| Contact Gender | Socket |
| Contacts included | No, order separately |
| Operating Voltage | 48 Vac, 60 Vdc |
| Current Rating | Up to 16 A (Signal Contacts) and up to 30 A (Power Contacts) |
| Operating Temperature | -55°C to +105°C |
| Insulator Resistance | 5000 Megaohms at 500 V dc |
| Durability | Up to 200 Mating Cycles |
| Flammability | UL94-V0 |
| Salt Spray | 48 hours |
| Vibration | 10 g's peak, 10 to 500 Hz, 9 hours |
| Physical Shock | 40 g's peak, 6msec., half-sine pulse |
| Insulator Material | Black Nylon |
| Coupling Nut Material | Nickel Plated Copper Alloy |
| Sealing Grommet Material | Silicone Rubber |
| Shell Material | Nickel Plated Zinc Alloy |
| Packaging | Single Pack |

Specifications and dimensions subject to change.



Downloaded from Arrow.com.