




Dimensions



Dimensions			
	A	B	C
Series B Thermistor	0.2mm	3mm Max	1.5mm Max

RADIAL GLASS NTC THERMISTORS – SERIES B

SPECIFICATIONS

- 2 to 500K Ohms Resistance @25°C
- Hermetically Sealed Package
- High Temperature Stability
- Available in $\pm 1\%$, $\pm 2\%$, $\pm 3\%$ or $\pm 5\%$ tolerance @25°C.
- Rated up to +250 °C.
- Low cost

RADIAL GLASS THERMISTORS

The NTC Chip hermetically sealed in a glass encapsulation package

FEATURES

- 2 to 500K Ohms Resistance @25°C
- Proven Stability
- Glass Encapsulation
- Low cost
- Temperature range -40°C to +250°C
- RoHS Compliant

APPLICATIONS

- Air conditioning systems
- Refrigeration control
- Assembly into probes for a wide variety of applications
- In environments where thermal shock and humidity are present
- Hot water boiler systems
- Sensor for engine temperature control

STABILITY

Reliability Tests	Standard	Test Condition	Delta R
Storage in Dry Heat	IEC 60068-2-2	Storage temperature: +250°C Duration: 1000 hours	< 3%
Storage in Damp Heat	IEC 60068-2-3	Temperature of air is 50°C & RH 93% Duration: 56 days.	< 2%
Rapid Temperature Cycling	IEC 60068-2-14	Lower Test Temperature -55°C Upper Test Temperature +200°C Number of Cycles 1000	< 2%

PRODUCT DEFINITION

Part Number	Resistance [Ω] @ +25°C	Tolerance @ +25°C	Beta Value 25/85	Beta Tolerance	Dissipation Constant in still air @ +25°C	Time response (Still Air)	Time response (Stirred Oil)
G2K3348B1	2,000	± 1%	3348	± 2%	0.8 mW/°C	5 Seconds	0.4 Seconds
G2K3499B1	2,000	± 1%	3499	± 2%	0.8 mW/°C	5 Seconds	0.4 Seconds
G5K3976B1	5,000	± 1%	3976	± 2%	0.8 mW/°C	5 Seconds	0.4 Seconds
G10K3435B1	10,000	± 1%	3435	± 2%	0.8 mW/°C	5 Seconds	0.4 Seconds
G10K3694B1	10,000	± 1%	3694	± 2%	0.8 mW/°C	5 Seconds	0.4 Seconds
G10K3976B1	10,000	± 1%	3976	± 2%	0.8 mW/°C	5 Seconds	0.4 Seconds
G30K3942B1	30,000	± 1%	3942	± 2%	0.8 mW/°C	5 Seconds	0.4 Seconds
G50K3976B1	50,000	± 1%	3976	± 2%	0.8 mW/°C	5 Seconds	0.4 Seconds
G100K4000B1	100,000	± 1%	4000	± 2%	0.8 mW/°C	5 Seconds	0.4 Seconds
G200K4261B1	200,000	± 1%	4261	± 3%	0.8 mW/°C	5 Seconds	0.4 Seconds
G500K4261B1	500,000	± 1%	4261	± 3%	0.8 mW/°C	5 Seconds	0.4 Seconds

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
1711 139th Lane NW
Andover, MN 55304
Tel: +1 763 689 4870
Fax: +1 763 689 5033
customer@te.com

EUROPE

Measurement Specialties (Europe), Ltd.,
a TE Connectivity Company
Ballybrit Business Park
Galway Ireland
Tel : +353-91-753238
Fax : +353-91-770789
Email: customer@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
No. 368 Wulian 1st Road
Gongxing Town
Shuangliu, Chengdu
Sichuan, 610200
China
Tel: +86 (0) 28 8573 9088
Fax: +86 (0) 28 8573 9070
Email: customer@te.com

te.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.