






This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.



PANEL THICKNESS



RECOMMENDED PANEL CUT-OUT



Customer drawing

POSITION	A	B	C	D	E	F(PITCH)
9	16.24	24.99	39.40	20.00	28.20	2.74
15	24.60	33.32	47.70	28.00	36.50	2.74
25	38.38	47.04	64.50	41.50	51.00	2.77
37	54.76	63.50	80.78	57.80	67.30	2.77

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1		New release	06/22/10	IP

D-SUB TECHNICAL DATA

SHELL : Steel, 1.25um(50u") min nickel
BODY : Glass filled thermoplastic.
flame retardant to UL94 V-0 color Black
PLATE : Glass filled thermoplastic.
flame retardant to UL94 V-0 color Black
CONTACTS : Brass, gold over 50u" min nickel.(According to the P/N)
SCREWLOCK : Brass, 50u" min nickel
REAR INSERT : Brass, 50u" min nickel
O RING : Silicone Color: Blue
EPOXY: Color: Black 300 V RMS at 50 Hz
ELECTRICAL : Voltage rating :
Current rating : 5A
Insulation resistance >5000 M Ohms
Contact resistance 20mOhms max.
MARKING : Amphenol logo
Manufacturing date(YYWW)



NOTE : Screw L=4.7 For Panel Thickness
Under X=1.2mm
Screw L=5.7 For Panel Thickness
Between X=1.2~2.0mm

PRODUCT CODE

L 17ED XX S 0 X

L: RoHS Compliance

17ED:
standard density series

Number of contacts
Standard density:
09, 15, 25, 37

Contact plating:
0: gold flash
1: 0.38um(15u")
2: 0.76um(30u")

Termination:
0: Solder cup

Contact type
S: Socket

UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL	DATE	Amphenol	
U.S.	METRIC	DRAWN	DATE		
.X +/-	0.50	Lamon He	06/22/10	Amphenol East Asia Limited	
.XX +/-	0.30	CHECKED	Lik Wang		
.XXX +/-	0.20	CHECKED		D-sub Waterproof, ED series female Solder cup type	
FRACTIONS +/-	2"				
ANGLES +/-				SIZE DRAWING NO. A4 C L17EDXXS0X	
FOR MATERIALS AND FINISHES SEE NOTES					
REMOVE SHARP EDGES				SCALE NONE SHEET 1 OF 1	
DIMENSIONS					
U.S. INCHES				REV. 1	
METRIC MM					