
Part Number : 15453532
Product Description : 2.54mm Pitch C-Grid PCB Connector, Surface Mount, High Profile, Dual Row, Vertical, 32 Circuits
Series Number : 71395
Status : Active
Product Category : PCB Headers and Receptacles
Engineering Part Number : 71395-0132



Documents and Resources

Drawings

015453532_sd.pdf

PK-70873-0662-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

713080001-AS-000.pdf

AS-71395-001-001.pdf

PS-71395-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)

Downloaded from Arrow.com.

EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	71395
Description	2.54mm Pitch C-Grid PCB Connector, Surface Mount, High Profile, Dual Row, Vertical, 32 Circuits
Application	Board-to-Board
Component Type	PCB Receptacle
Product Name	C-Grid
UPC	800755004120

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	2.5A

Downloaded from Arrow.com.

Voltage - Maximum	250V AC (RMS)

Physical

Circuits (Loaded)	32
Circuits (maximum)	32
Color - Resin	Black
Durability (mating cycles max)	50
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	No
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Number of Rows	2
Orientation	Vertical
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.381µm
Plating min - Termination	1.905µm
Polarized to Mating Part	No
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	REFLOW

Downloaded from Arrow.com.

Max-Cycle	1
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
C-Grid Vertical, Dual Row, Low Profile Headers	70246
C-Grid Vertical, Dual Row, Through Hole Headers without Peg	70567
C-Grid Right-Angle, Dual Row, Low Profile Headers	70247
C-Grid Right-Angle, Dual Row, Through Hole Headers	74162
C-Grid Vertical Dual Row Breakaway Headers	70280
C-Grid Vertical Dual Row Breakaway Headers with Retention Pin	70287
C-Grid Vertical, Dual Row, Surface Mount Breakaway Headers	71308
C-Grid Right-Angle Dual Row Breakaway Headers	70216
C-Grid Right-Angle, Dual Row, Low Profile, Breakaway Headers	71764

Downloaded from Arrow.com.