

80×80×25 mm

San Ace 80 9R type    Model 109R0812E401 is not certified.


General Specifications

- Material Frame: Plastic (Flammability: UL 94V-0), Impeller: Plastic (Flammability: UL 94V-1)
- Expected life See the table below. (L10 life: 90% survival rate for continuous operation in free air at 60°C, rated voltage)
Expected life at 40°C is for reference only.
- Motor protection function Locked rotor burnout protection, Reverse polarity protection
For details, please refer to p. 599.
- Dielectric strength 50/60 Hz, 500 VAC, for 1 minute (between lead wire conductors and frame)
- Insulation resistance 10 MΩ or more with a 500 VDC megger (between lead wire conductors and frame)
- Sound pressure level (SPL) At 1 m away from the air inlet
- Storage temperature -30 to +70°C (Non-condensing)
- Lead wire ⊕Red ⊖Black or Blue Sensor Yellow
- Mass 110 g

Specifications

The models listed below **have ribs and pulse sensors**. For models without ribs, append "1" to the end of model numbers.

Model no.	Rated voltage [V]	Operating voltage range [V]	Rated current [A]	Rated input [W]	Rated speed [min ⁻¹]	Max. airflow [m ³ /min] [CFM]	Max. static pressure [Pa] [inchH ₂ O]	SPL [dB (A)]	Operating temperature [°C]	Expected life [h]
» 109R0805F401	5	4.5 to 5.5	0.25	1.25	2600	0.92 32.5	28.4 0.114	26	-20 to +70	60000/60°C (90000/40°C)
» 109R0805M401			0.17	0.85	2350	0.83 29.3	22.5 0.09	23		
» 109R0812G401	12	10.8 to 13.2	0.37	4.44	4500	1.5 53.0	80.4 0.323	40	-20 to +60	40000/60°C (70000/40°C)
» 109R0812E401			0.24	2.88	3700	1.31 46.3	57.8 0.232	35		
» 109R0812S401		6 to 13.8	0.18	2.16	3400	1.2 42.4	48.0 0.193	34	-20 to +70	60000/60°C (90000/40°C)
» 109R0812H401			0.13	1.56	2900	1.03 36.4	35.3 0.142	29		
» 109R0812F401			0.11	1.32	2600	0.92 32.5	28.4 0.114	26		
» 109R0812M401			0.09	1.08	2350	0.83 29.3	22.5 0.09	23		
» 109R0812L401		7 to 13.8	0.06	0.72	1850	0.65 23.0	14.7 0.059	20		
» 109R0824G401			0.2	4.8	4500	1.5 53.0	80.4 0.323	40	-20 to +60	40000/60°C (70000/40°C)
» 109R0824S401	24	12 to 27.6	0.1	2.4	3400	1.2 42.4	48.0 0.193	34		
» 109R0824H401			0.07	1.68	2900	1.03 36.4	35.3 0.142	29	-20 to +70	60000/60°C (90000/40°C)
» 109R0824F401			0.06	1.44	2600	0.92 32.5	28.4 0.114	26		
» 109R0824M401			0.05	1.2	2350	0.83 29.3	22.5 0.09	23		
» 109R0824L401		14 to 27.6	0.04	0.96	1850	0.65 23.0	14.7 0.059	20		
» 109R0848K401			0.1	4.8	4600	1.56 55.1	88.4 0.355	41	-20 to +60	40000/60°C (70000/40°C)
» 109R0848S401	48	40.8 to 55.2	0.06	2.88	3400	1.2 42.4	48.0 0.193	34	-20 to +70	60000/60°C (90000/40°C)


Note 1: Sensor and control options are available for selection. Refer to the table on p. 623.

Note 2: The » mark indicates Short LeadTime Service applicable models. See p. 654 for details.


Airflow - Static Pressure Characteristics

109R0805F401 With pulse sensor


Operating voltage range


109R0805M401 With pulse sensor

Operating voltage range


109R0812G401 With pulse sensor


Operating voltage range




Airflow - Static Pressure Characteristics

109R0812E401 With pulse sensor


Operating voltage range


109R0812S401 With pulse sensor


Operating voltage range


109R0812H401 With pulse sensor


Operating voltage range


109R0812F401 With pulse sensor


Operating voltage range


109R0812M401 With pulse sensor


Operating voltage range


109R0812L401 With pulse sensor


Operating voltage range


109R0824G401 With pulse sensor


Operating voltage range


109R0824S401 With pulse sensor


Operating voltage range


109R0824H401 With pulse sensor


Operating voltage range


109R0824F401 With pulse sensor


Operating voltage range


109R0824M401 With pulse sensor

Operating voltage range


109R0824L401 With pulse sensor


Operating voltage range



Airflow - Static Pressure Characteristics


109R0848K401 With pulse sensor

Operating voltage range




109R0848S401 With pulse sensor


Operating voltage range



Dimensions (unit: mm) (With ribs)



Reference Dimensions of Mounting Holes and Vent Opening (unit: mm)



Options

Finger guards

page: p. 584

Model no.: 109-049E, 109-049H, 109-049C

Resin finger guards

page: p. 591

Model no.: 109-1002G

Resin filter kits

page: p. 592

Model no.: 109-1002F13 (13PPI), 109-1002F20 (20PPI),
109-1002F30 (30PPI), 109-1002F40 (40PPI)