


Technical drawing of a rectangular plate. The overall width is 1.12. The distance from the left edge to the center of the first hole is .19. The distance between the centers of the two holes is .75. The distance from the center of the second hole to the right edge is .38. The overall height is .62. The plate has two circular holes and two rectangular slots. The left hole is labeled 'w' and the right hole is labeled 'r'.

CATALOG LISTING	CIRCUIT MADE WITH TOGGLE LEVER IN 			ELECTRICAL DATA
	KEYWAY SIDE (1-2)	CENTER (1-2)	OPPOSITE KEYWAY (2-3)	
3INT394-1	ON	OFF	ON	LI91 15A 125, <u>250</u> , 277 VAC 1/2HP 125 VAC 1HP <u>250</u> , 277 VAC 5A 125 VAC "L"   
3INT394-2	OFF	NONE	ON	
3INT394-3	ON	NONE	ON	
3INT394-2I	NONE	OFF	ON	
3INT394-3I	NONE	ON	ON	
3INT394-5	MOM ON	OFF	ON	LI92 10A 125, <u>250</u> , 277 VAC 1/4HP 125 VAC, 1/2HP <u>250</u> , 277 VAC 3A 125 VAC "L"   
3INT394-6	MOM ON	NONE	OFF	
3INT394-7	MOM ON	OFF	MOM ON	
3INT394-8	MOM ON	NONE	ON	
3INT394-5I	NONE	ON	MOM ON	
3INT394-6I	MOM ON	OFF	NONE	



DESIGN UNITS: INCH			DRAWN	MBH	10AUG09	Honeywell					
TOLERANCES UNLESS NOTED:			CHECK	MJS	10AUG09						
NO PLACES	X	±	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH, TOGGLE					
ONE PLACE	.X	±									.030
TWO PLACE	.XX	±				.015					
THREE PLACE	.XXX	±	.005	INTERPRET PER ANSI 14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	CAGE CODE	DRAWING NAME	REV
ANGLES	X	±	-				B	I	-	31NT394 SERIES CHART 1	A
THIRD ANGLE PROJECTION			Pro/ENGINEER 2D			SCALE	NONE			SHEET	1 OF 1
											