



MLG0603S3N9BT000



Applications	 Commercial Grade
Feature	<div>Multilayer</div> Multilayer
	<div>Non-Mag Core</div> Non-Magnetic Core (Dielectric Ceramic)
Series Type	MLG
Status	 Production
Brand	TDK



Size	
Length(L)	0.60mm ±0.03mm
Width(W)	0.30mm ±0.03mm
Thickness Height	0.30mm ±0.03mm
Recommended Land Pattern (A)	0.25mm Nom.
Recommended Land Pattern (B)	0.30mm Nom.
Recommended Land Pattern (C)	0.30mm Nom.

Electrical Characteristics	
Inductance	3.9nH ±0.1nH at 100MHz
Rated Current	300mA
DC Resistance [Typ.]	270mΩ
DC Resistance [Max.]	400mΩ
Self Resonant Frequency [Min.]	5GHz
Self Resonant Frequency [Typ.]	6.6GHz
Q [Min.]	5 at 100MHz
Q [Typ.]	





Other	
Operating Temp. Range	-55 to 125°C
Soldering Method	Reflow
	Iron Soldering
AEC-Q200	NO
Packing	Punched (Paper)Taping [180mm Reel, Tape width 8mm]
Package Quantity	15000pcs
Weight	0.0002g

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

MLG0603S3N9BT000



Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)





Associated Images

