






PRODUCT NUMBER
10130077-001LF



PACKING DIRECTLY AFTER THE JOINT.



SPEC.	2.54*6*(50M-150M)-U		
BOM	Conductor	Spec	CSN76157 _(Tin 0.076*1.57mm)
		Plated	Sn≥40u”
	Insulation	NO Marking	100um
		NO Marking	100um
	Reinforcing tape		
	NO MARKING		
Code	Item	Dimension	Tolerance
PH	Pitch	2.54	±0.13
N	Number of Conductors	6	
TL	Total Length	50M-150M	
IL	Insulation Length		
S1	Strip Length		
S2	Strip Length		
R1	Reinforcing Length		
R2	Reinforcing Length		
TP	Total Pitch	12.7	±0.13
W	Total Width	17.78	±0.13
M	Margin Width	2.54	±0.13
IT	Cable Thickness	0.28	±0.05
T	Terminal Thickness		
CT	Conductor Thickness	0.076	±0.013
CW	Conductor Width	1.57	±0.07

Note:




- Product scope of the total length is 50M to 150M, after the joint packing directly.
- Storage environment: Temperature: 15°C~30°C. Humidity: Max. 75%RH.
- Rated voltage: 300V. Test voltage: 500V.
- Rated current: 1.5A Max. 1A Min. per conductor.
- Conductor resistance: 0.83Ω/m; Contact resistance: Less than 40mΩ.
- Specification: IPC Standard, FC-220 B Cables type A or B, tolerance class IV.
- Additional Cable Specifications: See technical drawings TA-264, TA-371.
- Insulation resistance: 100MΩ (DC500V, 60sec.).
- Operating temperature range: -40°C to 120°C.
- Insulated material is PET.

mat'l. code				surface	tolerance	projection	product family			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title			
A		TAI	2014-07-02	angles	500 < TL ±8.0					
					300 < TL ≤ 500 ±5.0		FLEXIBLE FLAT CABLE 6 CONDUCTORS			
					X*±3'					
				dr	KENNY TAI	2013-12-2	dwg no		sheet 1 of 2	
				enr	KENNY TAI	2013-12-2				
				chr	KENNY TAI	2014-05-08	10130077		A4	
				appd	PM ZHENG	2014-07-02				
sheet index	revision sheet	A	A				type		CUSTOMER Drawing	
		1	2							




PRODUCT NUMBER

10130077-002LF






PACKING DIRECTLY AFTER THE JOINT.



SPEC.	2.54*8*(50M-150M)		
BOM	Conductor	Spec	CSN76157(tin 0.076±1.57mm)
		Plated	Sn ≥40u”
	Insulation	NO Marking	100um
		NO Marking	100um
	Reinforcing tape		
	NO MARKING		
Code	Item	Dimension	Tolerance
PH	Pitch	2.54	±0.13
N	Number of Conductors	8	
TL	Total Length	50M-150M	
IL	Insulation Length		
S1	Strip Length		
S2	Strip Length		
R1	Reinforcing Length		
R2	Reinforcing Length		
TP	Total Pitch	17.78	±0.13
W	Total Width	22.86	±0.13
M	Margin Width	2.54	±0.13
IT	Cable Thickness	0.28	±0.05
T	Terminal Thickness		
CT	Conductor Thickness	0.076	±0.013
CW	Conductor Width	1.57	±0.07

Note:

1. Product scope of the total length is 50M to 150M, after the joint packing directly.
2. Storage environment: Temperature: 15°C~30°C. Humidity: Max. 75%RH.
3. Rated voltage: 300V. Test voltage: 500V.
4. Rated current: 1.5A Max. 1A Min. per conductor.
5. Conductor resistance: 0.63Ω/m; Contact resistance: Less than 40mΩ.
6. Specification: IPC Standard, FC-220 B Cables type A or B, tolerance class IV.
7. Additional Cable Specifications: See technical drawings TA-264, TA-371.
8. Insulation resistance: 100MΩ (DC500V, 60sec.).
9. Operating temperature range: -40°C to 120°C.
10. Insulated material is PET.

mat'l. code					surface <input checked="" type="checkbox"/>		tolerance		projection 		product family										
ltr		ecn		no	dr	date		tolerances unless otherwise specified						title FLEXIBLE FLAT CABLE 8 CONDUCTORS							
								angles		lineal		500 < TL ±8.0									
										300 < TL ≤ 500 ±5.0											
								X°±3°				200 < TL ≤ 300 ±3.0									
								dr	KENNY TAI		2013-12-2				dwg no		sheet 2 of 2		size		
								engr	KENNY TAI		2013-12-2				10130077		A4				
								chr	KENNY TAI		2014-05-08				type CUSTOMER Drawing						
								appd	PM ZHENG		2014-07-02										
sheet index		revision sheet		A	A		1		2												