


SCRH105RY

SMD POWER INDUCTORS





• Features

1. Magnetically shielded construction
2. Excellent Power Density
3. Engineered to Provide High Efficiency

ELECTRICAL CHARACTERISTICS



Part Number	Inductance (uH) (1)	Test Frequency	DC Resistance (Ω MAX) (2)	Saturation Current ⁽³⁾ (A)	Temperature Current ⁽⁴⁾ (A)
SCRH105RY-0R8	0.8	100KHZ	5m	13.5	11.50
SCRH105RY-1R5	1.5	100KHZ	6m	10.5	10.30
SCRH105RY-2R2	2.2	100KHZ	8m	9.25	9.20
SCRH105RY-3R3	3.3	100KHZ	11m	8.80	8.20
SCRH105RY-4R7	4.7	100KHZ	13m	8.00	7.30
SCRH105RY-6R8	6.8	100KHZ	18m	5.50	6.20
SCRH105RY-8R2	8.2	100KHZ	20m	5.00	5.50
SCRH105RY-100	10	100KHZ	26m	4.45	4.50
SCRH105RY-120	12	100KHZ	33m	4.00	4.00
SCRH105RY-150	15	100KHZ	41m	3.60	3.80
SCRH105RY-180	18	100KHZ	46m	3.20	3.42
SCRH105RY-220	22	100KHZ	61m	2.95	3.07
SCRH105RY-270	27	100KHZ	69m	2.70	2.76
SCRH105RY-330	33	100KHZ	84m	2.40	2.48
SCRH105RY-390	39	100KHZ	106m	2.30	2.35
SCRH105RY-470	47	100KHZ	130m	2.00	2.11
SCRH105RY-560	56	100KHZ	149m	1.90	2.00
SCRH105RY-680	68	100KHZ	201m	1.65	1.70
SCRH105RY-820	82	100KHZ	227m	1.50	1.53
SCRH105RY-101	100	100KHZ	253m	1.35	1.35
SCRH105RY-121	120	100KHZ	303m	1.28	1.28
SCRH105RY-151	150	100KHZ	370m	1.12	1.15
SCRH105RY-181	180	100KHZ	419m	1.04	1.09
SCRH105RY-221	220	100KHZ	500m	0.94	0.93
SCRH105RY-271	270	100KHZ	672m	0.84	0.85
SCRH105RY-331	330	100KHZ	812m	0.75	0.76
SCRH105RY-391	390	100KHZ	953m	0.70	0.68
SCRH105RY-471	470	100KHZ	1.30	0.60	0.60
SCRH105RY-561	560	100KHZ	1.43	0.54	0.57
SCRH105RY-681	680	100KHZ	1.60	0.52	0.54
SCRH105RY-821	820	100KHZ	1.77	0.50	0.50
SCRH105RY-102	1000	100KHZ	1.99	0.48	0.46



- (1). Inductance tolerance $\pm 30\%$ tested at 0.25V, 0ADC and 25°C
- (2). DCR measured at 25°C.
- (3). The DC current at which the inductance decreases by 35% from its initial value.
- (4). The DC current that results in a 40°C temperature rise from 25°C ambient.

[Click here for QUANTITY PER REEL & PACKING INFORMATION](#)

Custom versions available upon request.

© 2019 Signal Transformer – Specification subject to change without notice. 12.19



belfuse.com/signal

128 Atlantic Avenue, Lynbrook, NY 11563
Toll Free 866-239-5777 • Tel 516-239-5777 • Fax 516-239-7208
Sales@signaltransformer.com • techhelp@signaltransformer.com

Please read our datasheet & drawing disclaimer [here](#).