







X (2:1)

Steckgesicht n.
Contact face acc.to
IEC 61076-2-101



Crimpkontakte separat bestellen
Order contacts separately

Kabel ϕ / Cable ϕ			Leiterquerschnitt Wire gauge	Bestell-Nr. Part-No.
5,5-7,2mm	4,5-5,4mm	7.0-8.8mm		
Dichtung / Sealing			AWG 26-22	09 67 000 5576
schwarz/black	transparent	beige	AWG 24-20	09 67 000 8576



All Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Maße/Free size tolerances	
				Dat.	Name	1:1	M12 crimp WDF geschirmt, Stift, D-kodiert, 4-polig Panel feed through shielded, Stift, D-coded, 4-pole
EC03244	20.05.11	DY	Detail.	25.08.08	Ho		
EC02795	28.01.11	DY	Insp.		Bei		
EC01106	23.11.09	DY	Stand.				
414337	17.06.09	DY	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP			TB 21 03 882 1425	Blatt/ page
414099							
Mod.	Dat.	Name				Sub.	



Blatt/ page

Sub.