


PCB LAYOUT: COMPONENT SIDE
TYPICAL PCB THICKNESS: .062/(1.57)

A-4030-N * (* *)
NO. OF CKTS.
VERSION
LETTER CHANGES WHEN PIN
NO. OR PRESS DIM. CHANGES.
PLATING CODE
SEE NOTE 2

SECONDARY OPERATIONS	
CODE	PACKAGE
BLANK	BULK PER PK-4030-001
A	TUBE PER PK-44743-002

CKTS. NO. OF	DIM. B	DIM. A
2	.100 ± .002 (2.54 ± .05)	.190 ± .008 (4.83 ± .20)
3	.200 ± .005 (5.08 ± .13)	.290 ± .008 (7.37 ± .20)
4	.300 ± .005 (7.62 ± .13)	.390 ± .008 (9.91 ± .20)
5	.400 ± .005 (10.16 ± .13)	.490 ± .008 (12.45 ± .20)
6	.500 ± .006 (12.70 ± .15)	.590 ± .009 (14.99 ± .23)
7	.600 ± .006 (15.24 ± .15)	.690 ± .009 (17.53 ± .23)
8	.700 ± .006 (17.78 ± .15)	.790 ± .009 (20.07 ± .23)
9	.800 ± .007 (20.32 ± .18)	.890 ± .010 (22.61 ± .25)
10	.900 ± .007 (22.86 ± .18)	.990 ± .010 (25.15 ± .25)
11	1.000 ± .007 (25.40 ± .18)	1.090 ± .010 (27.69 ± .25)
12	1.100 ± .008 (27.94 ± .20)	1.190 ± .011 (30.23 ± .28)
13	1.200 ± .008 (30.48 ± .20)	1.290 ± .011 (32.77 ± .28)
14	1.300 ± .008 (33.02 ± .20)	1.390 ± .011 (35.31 ± .28)
15	1.400 ± .008 (35.56 ± .20)	1.490 ± .011 (37.85 ± .28)
16	1.500 ± .008 (38.10 ± .20)	1.590 ± .011 (40.39 ± .28)
17	1.600 ± .009 (40.64 ± .23)	1.690 ± .012 (42.93 ± .30)
18	1.700 ± .009 (43.18 ± .23)	1.790 ± .012 (45.47 ± .30)
19	1.800 ± .009 (45.72 ± .23)	1.890 ± .012 (48.01 ± .30)
20	1.900 ± .009 (48.26 ± .23)	1.990 ± .012 (50.55 ± .30)
21	2.000 ± .010 (50.80 ± .25)	2.090 ± .013 (53.09 ± .33)
22	2.100 ± .010 (53.34 ± .25)	2.190 ± .013 (55.63 ± .33)
23	2.200 ± .010 (55.88 ± .25)	2.290 ± .013 (58.17 ± .33)
24	2.300 ± .010 (58.42 ± .25)	2.390 ± .013 (60.71 ± .33)
25	2.400 ± .011 (60.96 ± .28)	2.490 ± .014 (63.25 ± .36)
26	2.500 ± .011 (63.50 ± .28)	2.590 ± .014 (65.79 ± .36)
27	2.600 ± .011 (66.04 ± .28)	2.690 ± .014 (68.33 ± .36)
28	2.700 ± .011 (68.58 ± .28)	2.790 ± .014 (70.87 ± .36)

NOTES:

- MATERIAL: WAFER: NYLON, UL94V-0, COLOR: WHITE
PINS: COPPER ALLOY
- FINISH: 102: .000200/0.00508 MIN TIN OVER .000100/0.00254 MIN COPPER
132: .000200/0.00508 MIN TIN OVER .000200/0.00508 MIN COPPER
501: .000020/0.00051 MIN GOLD OVER .000030/0.00076 MIN NICKEL
503: .000030/0.00076 MIN GOLD OVER .000050/0.00127 MIN NICKEL
516: .000010/0.00025 MIN GOLD OVER .000030/0.00076 MIN NICKEL
- PARTS CONFORM TO PRODUCT SPECIFICATION PS-10-07.
- PACKAGING INFORMATION: SEE LEGEND
- PINS MUST CONFORM TO SOLDERABILITY SPECIFICATION SMES-152.
- PIN PUSH OUT FORCE: 2 LBS. MIN.
- PARTS ARE STACKABLE END TO END AND SIDE TO SIDE ON .100/(2.54) CENTERS.
- SEE SDA-4030 FOR STANDARD CATALOG PRODUCTS.
- THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

ADD 22-03-5117 EC NO: UCP2010-0896 DRWN:KIPPER 2009/10/16 CHKD:SSOUSEK 2009/10/20 APPR:FSMITH 2009/10/20 C15	DESCRIPTION	REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY SAMIEC	DATE 06/10/88	TITLE KK 100 HEADER FLAT CUSTOM PRODUCTS			
				4 PLACES ± ---	± ---	CHECKED BY PATEL	DATE 06/10/88	MOLEX INCORPORATED			
				3 PLACES ± ---	± ---	APPROVED BY LENZ	DATE 06/10/88	SDA-4030-002			
				2 PLACES ± ---	± ---	MATERIAL NO.		DOCUMENT NO.			SHEET NO. 1 OF 16
				1 PLACE ± ---	± ---	SEE CHART		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
				ANGULAR ±1/2°		SIZE C					
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							

[illegible]