

30300500421 - 303 Series



Series: 303

Questions? Contact Littelfuse Support

Fuse 303 Datasheet

- Features
- Lead-free/RoHS Compliant
 - Reduced PCB space requirements
 - Direct solderable or plug-in versions
 - Internationally approved
 - Low internal resistance
 - Shocksafe casing
 - Vibration resistant

Check Stock

Order Samples

NEW! Product Selection Guide eCatalog Read Now

Electronics News and Information SIGN UP NOW

Electrical Characteristics	Technical Resources	Environmental Info
Property (Mouseover for details)	Value	
Ampere Rating (A)	0.05	
Nominal Melting I²T (A²sec)	0.00007	
Interrupting Rating	50A@125VAC	
Min Operating Temp °C	-25	
Max Operating Temp (°C)	70	
Moisture Sensitivity Level	MIL-STD-202 Method 106	
Nominal Power Dissipation (W)	40	
Nominal Voltage Drop (mV)	800	
Nominal Cold Resistance (Ohms)	2.92	
Opening	Fast-Acting (F)	
Package Size	TR3/MICRO (6x8mm)	
VAC (V)	125	

Connect with Littelfuse

Sign up to receive special offers and news

Enter your email Submit

For more details about how we use your information, check our Privacy Statement.

in G+ f t y d i i s r

Mobile Site

About Littelfuse

About Littelfuse

Conflict Free Statement

History

Investor Relations

Legal

Press Room

Privacy Statement

Supply Chain Transparency

Website Feedback

Explore Littelfuse

Capabilities Brochures

Careers

Check Distributor Stock

Competitor Cross Reference

Industries

Order Samples

Products

Services

Technical Resources

Application Designs

Education

FAQs

iDesign™

Littelfuse University

Product Catalogs

Quality Documents

Technical Documents