


# PTRA084858NF

Thermally-Enhanced High Power RF LDMOS FET  
615 W, 48 V, 730 – 960 MHz

## Description

The PTRA084858NF is a 615-watt LDMOS FET intended for use in multistandard cellular power amplifier applications in the 730 to 960 MHz frequency band. Features include input and output matching, high gain and a thermally-enhanced plastic overmold package for cool and reliable operation. Manufactured with an advanced LDMOS process, this device provides excellent thermal performance and superior reliability.

PTRA084858NF  
Package PG-HBSOF-6-3



## Features

- Broadband Input and output matching
- Asymmetric Doherty design
  - Main:  $P_{1dB} = 211\text{ W}$  Typ
  - Peak:  $P_{1dB} = 468\text{ W}$  Typ
- Typical pulsed CW performance: 10  $\mu\text{s}$  pulse width, 10% duty cycle, 820 MHz, 48 V, Doherty fixture
  - Gain = 19.5 dB
  - Efficiency = 52%
  - Output power at  $P_{1dB} = 214\text{ W}$
  - Output power at  $P_{3dB} = 615\text{ W}$
- Capable of handling 10:1 VSWR @ 48 V, 87 W (CW) output power
- Integrated ESD protection
- Human Body Model Class 1C (per ANSI/ESDA/JEDEC JS-001)
- Pb-free and RoHS-compliant

## RF Characteristics

### Single-carrier WCDMA Specifications (tested in the Doherty test fixture)

$V_{DD} = 48\text{ V}$ ,  $I_{DQ} = 500\text{ mA}$ ,  $V_{GS(PEAK)} = 2\text{ V}$ ,  $P_{OUT} = 87\text{ W}$  avg,  $f = 820\text{ MHz}$   
 3GPP signal, channel bandwidth = 3.84 MHz, peak/average = 10 dB @ 0.01% CCDF

| Characteristic               | Symbol   | Min  | Typ | Max | Unit |
|------------------------------|----------|------|-----|-----|------|
| Gain                         | $G_{ps}$ | 18.2 | 19  | —   | dB   |
| Drain Efficiency             | $\eta_D$ | 46   | 50  | —   | %    |
| Adjacent Channel Power Ratio | ACPR     | —    | -36 | -30 | dBc  |
| Output PAR @ 0.01% CCDF      | OPAR     | 7    | 7.4 | —   | dB   |

All published data at  $T_{CASE} = 25^\circ\text{C}$  unless otherwise indicated

ESD: Electrostatic discharge sensitive device—observe handling precautions!



## DC Characteristics

| Characteristics                | Conditions                                               | Symbol        | Min   | Typ  | Max  | Unit          |
|--------------------------------|----------------------------------------------------------|---------------|-------|------|------|---------------|
| Drain-source Breakdown Voltage | $V_{GS} = 0\text{ V}$ , $I_{DS} = 10\text{ mA}$          | $V_{(BR)DSS}$ | 105   | —    | —    | V             |
| Drain Leakage Current          | $V_{DS} = 48\text{ V}$ , $V_{GS} = 0\text{ V}$           | $I_{DSS}$     | —     | —    | 1    | $\mu\text{A}$ |
|                                | $V_{DS} = 105\text{ V}$ , $V_{GS} = 0\text{ V}$          |               | —     | —    | 10   | $\mu\text{A}$ |
| Gate Leakage Current           | $V_{GS} = 10\text{ V}$ , $V_{DS} = 0\text{ V}$           | $I_{GSS}$     | —     | —    | 1    | $\mu\text{A}$ |
| On-State Resistance            | (main) $V_{GS} = 10\text{ V}$ , $V_{DS} = 0.1\text{ V}$  | $R_{DS(on)}$  | 0.025 | 0.08 | 0.41 | $\Omega$      |
|                                | (peak) $V_{GS} = 10\text{ V}$ , $V_{DS} = 0.1\text{ V}$  | $R_{DS(on)}$  | 0.01  | 0.05 | 0.38 | $\Omega$      |
| Operating Gate Voltage         | (main) $V_{DS} = 48\text{ V}$ , $I_{DQ} = 500\text{ mA}$ | $V_{GS}$      | 3.4   | 3.7  | 4    | V             |
|                                | (peak) $V_{DS} = 48\text{ V}$ , $I_{DQ} = 500\text{ mA}$ | $V_{GS}$      | —     | 2    | —    | V             |

## Maximum Ratings

| Parameter                 | Symbol    | Value       | Unit               |
|---------------------------|-----------|-------------|--------------------|
| Drain-source Voltage      | $V_{DSS}$ | 105         | V                  |
| Gate-source Voltage       | $V_{GS}$  | –6 to +12   | V                  |
| Operating Voltage         | $V_{DD}$  | 0 to +55    | V                  |
| Junction Temperature      | $T_J$     | 225         | $^{\circ}\text{C}$ |
| Storage Temperature Range | $T_{STG}$ | –65 to +150 | $^{\circ}\text{C}$ |

1. Operation above the maximum values listed here may cause permanent damage. Maximum ratings are absolute ratings; exceeding only one of these values may cause irreversible damage to the component. Exposure to absolute maximum rating conditions for extended periods may affect device reliability. For reliable continuous operation, the device should be operated within the operating voltage range ( $V_{DD}$ ) specified above.
2. Parameters values can be affected by end application and product usage. Values may change over time.

## Thermal Characteristics

Thermal resistance, junction to case ( $T_{CASE} = 70^{\circ}\text{C}$ ,  $f = 790\text{ MHz}$ )

| Characteristics                                                                                  | Symbol          | Value | Unit                 |
|--------------------------------------------------------------------------------------------------|-----------------|-------|----------------------|
| Thermal Resistance (main) $P_{DISS} = 56\text{ W CW}$ , $48\text{ V}$ , $I_{DQ} = 500\text{ mA}$ | $R_{\theta JC}$ | 0.52  | $^{\circ}\text{C/W}$ |
| (peak) $P_{DISS} = 215\text{ W CW}$ , $48\text{ V}$ , $V_{GS} = 2.0\text{ V}$                    | $R_{\theta JC}$ | 0.23  | $^{\circ}\text{C/W}$ |

## Moisture Sensitivity Level

| Level | Test Standard       | Package Temperature | Unit               |
|-------|---------------------|---------------------|--------------------|
| 3     | IPC/JEDEC J-STD-020 | 260                 | $^{\circ}\text{C}$ |


## Ordering Information

| Type and Version   | Order Code         | Package      | Shipping             |
|--------------------|--------------------|--------------|----------------------|
| PTRA084858NF V1 R5 | PTRA084858NF-V1-R5 | PG-HBSOF-6-3 | Tape & Reel, 500 pcs |


**Typical Performance** (data taken in the production test fixture)

**Single-carrier WCDMA Drive-up**


$V_{DD} = 48\text{ V}$ ,  $I_{DQ(MAIN)} = 500\text{ mA}$ ,  
 $V_{GS(PEAK)} = 2\text{ V}$ ,  $f = 820\text{ MHz}$   
 3GPP WCDMA signal,  
 10 dB PAR, 3.84 MHz bandwidth


**Single-carrier WCDMA Broadband Performance**


$V_{DD} = 48\text{ V}$ ,  $I_{DQ} = 500\text{ mA}$ ,  $V_{GS(PEAK)} = 2.0\text{ V}$   
 $P_{OUT} = 49.4\text{ dBm}$ ,  
 3GPP WCDMA signal, 10 dB PAR


**Single-carrier WCDMA Broadband Performance**



$V_{DD} = 48\text{ V}$ ,  $I_{DQ} = 500\text{ mA}$ ,  $V_{GS(PEAK)} = 2\text{ V}$   
 $P_{OUT} = 49.4\text{ dBm}$ ,  
 3GPP WCDMA signal, 10 dB PAR


**CW Performance**

$V_{DD} = 48.0\text{ V}$ ,  $I_{DQ} = 500\text{ mA}$ ,  $V_{GS(PEAK)} = 2.0\text{ V}$



## Typical Performance (cont.)



## Load Pull

Main side pulsed CW signal: 12  $\mu\text{sec}$ , 10% duty cycle; 48 V,  $I_{DQ} = 400 \text{ mA}$ , class AB

|            |                    | $P_{1dB}$          |           |                 |               |              |                      |           |                 |               |              |
|------------|--------------------|--------------------|-----------|-----------------|---------------|--------------|----------------------|-----------|-----------------|---------------|--------------|
|            |                    | Max Output Power   |           |                 |               |              | Max Drain Efficiency |           |                 |               |              |
| Freq [MHz] | $Z_S$ [ $\Omega$ ] | $Z_L$ [ $\Omega$ ] | Gain [dB] | $P_{OUT}$ [dBm] | $P_{OUT}$ [W] | $\eta_D$ [%] | $Z_L$ [ $\Omega$ ]   | Gain [dB] | $P_{OUT}$ [dBm] | $P_{OUT}$ [W] | $\eta_D$ [%] |
| 760        | $1.5 - j1.0$       | $2.7 - j0.6$       | 22.2      | 53.30           | 214           | 56.3         | $5.1 + j0.9$         | 23.8      | 52.10           | 162           | 67.3         |
| 790        | $1.4 - j1.9$       | $2.6 - j0.4$       | 22.1      | 53.30           | 214           | 57.0         | $4.8 + j1.3$         | 23.8      | 52.00           | 158           | 67.2         |
| 820        | $1.4 - j2.6$       | $2.5 - j0.4$       | 21.8      | 53.20           | 209           | 56.3         | $4.5 + j1.5$         | 23.6      | 51.90           | 155           | 66.9         |

|            |                    | $P_{3dB}$          |           |                 |               |              |                      |           |                 |               |              |
|------------|--------------------|--------------------|-----------|-----------------|---------------|--------------|----------------------|-----------|-----------------|---------------|--------------|
|            |                    | Max Output Power   |           |                 |               |              | Max Drain Efficiency |           |                 |               |              |
| Freq [MHz] | $Z_S$ [ $\Omega$ ] | $Z_L$ [ $\Omega$ ] | Gain [dB] | $P_{OUT}$ [dBm] | $P_{OUT}$ [W] | $\eta_D$ [%] | $Z_L$ [ $\Omega$ ]   | Gain [dB] | $P_{OUT}$ [dBm] | $P_{OUT}$ [W] | $\eta_D$ [%] |
| 760        | $1.5 - j1.0$       | $2.7 - j0.8$       | 20.3      | 54.10           | 257           | 58.9         | $5.4 + j1.3$         | 21.9      | 52.50           | 178           | 68.5         |
| 790        | $1.4 - j1.9$       | $2.6 - j0.7$       | 20.1      | 54.10           | 257           | 59.2         | $4.8 + j1.9$         | 21.8      | 52.30           | 170           | 68.6         |
| 820        | $1.4 - j2.6$       | $2.6 - j0.7$       | 19.9      | 54.00           | 251           | 59.2         | $4.5 + j1.7$         | 21.6      | 52.40           | 174           | 68.3         |

See next page for peak side load pull

## Load Pull

Peak side pulsed CW signal: 12  $\mu$ sec, 10% duty cycle; 48 V,  $V_{GS(PEAK)} = 2$  V, class C

|            |                             | P <sub>1dB</sub>            |           |                        |                      |              |                             |           |                        |                      |              |
|------------|-----------------------------|-----------------------------|-----------|------------------------|----------------------|--------------|-----------------------------|-----------|------------------------|----------------------|--------------|
|            |                             | Max Output Power            |           |                        |                      |              | Max Drain Efficiency        |           |                        |                      |              |
| Freq [MHz] | Z <sub>s</sub> [ $\Omega$ ] | Z <sub>l</sub> [ $\Omega$ ] | Gain [dB] | P <sub>OUT</sub> [dBm] | P <sub>OUT</sub> [W] | $\eta_D$ [%] | Z <sub>l</sub> [ $\Omega$ ] | Gain [dB] | P <sub>OUT</sub> [dBm] | P <sub>OUT</sub> [W] | $\eta_D$ [%] |
| 760        | 0.7 – j1.8                  | 1.1 + j0.1                  | 17.7      | 56.50                  | 447                  | 61.5         | 1.1 + j1.3                  | 18.6      | 53.90                  | 245                  | 75.2         |
| 790        | 0.7 – j2.2                  | 1.1 + j0.1                  | 17.3      | 56.50                  | 447                  | 61.2         | 1.1 + j1.3                  | 18.2      | 54.00                  | 251                  | 74.5         |
| 820        | 0.8 – j2.5                  | 1.0 + j0.2                  | 17.5      | 56.70                  | 468                  | 64.8         | 1.0 + j1.3                  | 18.3      | 54.30                  | 269                  | 77.3         |

|            |                             | P <sub>3dB</sub>            |           |                        |                      |              |                             |           |                        |                      |              |
|------------|-----------------------------|-----------------------------|-----------|------------------------|----------------------|--------------|-----------------------------|-----------|------------------------|----------------------|--------------|
|            |                             | Max Output Power            |           |                        |                      |              | Max Drain Efficiency        |           |                        |                      |              |
| Freq [MHz] | Z <sub>s</sub> [ $\Omega$ ] | Z <sub>l</sub> [ $\Omega$ ] | Gain [dB] | P <sub>OUT</sub> [dBm] | P <sub>OUT</sub> [W] | $\eta_D$ [%] | Z <sub>l</sub> [ $\Omega$ ] | Gain [dB] | P <sub>OUT</sub> [dBm] | P <sub>OUT</sub> [W] | $\eta_D$ [%] |
| 760        | 0.7 – j1.8                  | 1.1 + j0.0                  | 15.6      | 57.20                  | 525                  | 62.7         | 1.1 + j1.3                  | 16.6      | 54.60                  | 288                  | 74.5         |
| 790        | 0.7 – j2.2                  | 1.1 + j0.0                  | 15.2      | 57.20                  | 525                  | 62.4         | 1.1 + j1.3                  | 16.3      | 54.80                  | 302                  | 74.7         |
| 820        | 0.8 – j2.5                  | 1.1 + j0.2                  | 15.4      | 57.30                  | 537                  | 65.4         | 1.0 + j1.3                  | 16.3      | 54.80                  | 302                  | 77.0         |


## Reference Circuit, 760 – 820 MHz

### Reference Circuit Assembly

|                       |                                                                         |
|-----------------------|-------------------------------------------------------------------------|
| DUT                   | PTRA084858NF                                                            |
| Test Fixture Part No. | LTA/PTRA084858NF-V1                                                     |
| PCB                   | Rogers 4350, 0.508 mm [0.020"] thick, 2 oz. copper, $\epsilon_r = 3.66$ |

## Reference Circuit continued next page

## Reference Circuit, 760 – 820 MHz (cont.)



Reference circuit assembly diagram (not to scale)

## Bias Sequencing

### Bias ON

1. Ensure RF is turned off
2. Apply pinch-off voltage of 0 V to the gate
3. Apply nominal drain voltage
4. Bias gate to desired quiescent drain current
5. Apply RF

### Bias OFF


1. Turn RF off
2. Apply pinch-off voltage of 0 V to the gate
3. Turn off drain voltage
4. Turn off gate voltage

Reference Circuit, 760 – 820 MHz (cont.)


Components Table

| Component                    | Description             | Manufacturer                    | P/N                 |
|------------------------------|-------------------------|---------------------------------|---------------------|
| Input                        |                         |                                 |                     |
| C101, C102                   | Capacitor, 18 pF        | ATC                             | ATC600F180JT250XT   |
| C103, C107, C111, C112       | Capacitor, 100 pF       | ATC                             | ATC600F101JT250XT   |
| C104, C113                   | Capacitor, 1 µF         | TDK Corporation                 | C4532X7R2A105M230KA |
| C105, C114                   | Capacitor, 10 µF, 100 V | Murata Electronics              | GRM32EC72A106KE05L  |
| C106                         | Capacitor, 10 pF        | ATC                             | ATC600F100JT250XT   |
| C108, C110                   | Capacitor, 5.6 pF       | ATC                             | ATC600F5R6CT250XT   |
| C109                         | Capacitor, 18 pF        | ATC                             | ATC600F180JT250XT   |
| R101                         | Resistor, 8.2 ohms      | Panasonic Electronic Components | ERJ-8RQJ8R2V        |
| R102                         | Resistor, 10 ohms       | Panasonic Electronic Components | ERJ-8GEYJ100V       |
| R103                         | Resistor, 50 ohms       | Anaren                          | C16A50Z4            |
| U1                           | Hybrid Coupler          | RN2 Technolgies Co              | CMX07Q01            |
| Output                       |                         |                                 |                     |
| C201, C212, C213, C218, C219 | Capacitor, 10 µF, 100 V | Murata Electronics              | GRM32EC72A106KE05L  |
| C202                         | Capacitor, 18 pF        | ATC                             | ATC600F180JT250XT   |
| C203, C215                   | Capacitor, 12 pF        | ATC                             | ATC600F120JT250XT   |
| C204, C205                   | Capacitor, 6.8 pF       | ATC                             | ATC600F6R8JT250XT   |
| C206, C207                   | Capacitor, 47 pF        | ATC                             | ATC100B470JW500XB   |
| C208, C209, C210, C216       | Capacitor, 100 pF       | ATC                             | ATC600F101JT250XT   |
| C211, C217                   | Capacitor, 1 µF         | TDK Corporation                 | C4532X7R2A105M230KA |
| C214, C220                   | Capacitor, 100 µF       | Panasonic Electronic Components | EEE-FP1V101A        |

Pinout Diagram (top view)



## Package Outline Specifications



## Notes & Disclaimer

---

MACOM Technology Solutions Inc. ("MACOM"). All rights reserved.

These materials are provided in connection with MACOM's products as a service to its customers and may be used for informational purposes only. Except as provided in its Terms and Conditions of Sale or any separate agreement, MACOM assumes no liability or responsibility whatsoever, including for (i) errors or omissions in these materials; (ii) failure to update these materials; or (iii) conflicts or incompatibilities arising from future changes to specifications and product descriptions, which MACOM may make at any time, without notice. These materials grant no license, express or implied, to any intellectual property rights.

THESE MATERIALS ARE PROVIDED "AS IS" WITH NO WARRANTY OR LIABILITY, EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHT, ACCURACY OR COMPLETENESS, OR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES WHICH MAY RESULT FROM USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.