

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638244600

Status:

Active

Overview:

Application Tooling

Description:

Extraction Tool for Nano-Fit Power Connectors and Crimp Terminals, 20-26 AWG

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Taxonomy

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207121

See Tooling Specification (PDF) Above

Extraction

Global

Manual

applicationtooling@molex.com

Application Tooling

N/A

Crimp Presses and Crimp Hand T

Extraction Hand Tool

889056010399

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

143.370/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-638244600-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

207121 Series

Application Tooling Description	FAQ Product #
Nano-Fit Crimp Terminal, Female, 2.54µm Matte Tin (Sn) Plating, 24-26 AWG	1053001100
Nano-Fit Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 24-26 AWG	1053001200
Nano-Fit Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 24-26 AWG	1053001300
Nano-Fit Crimp Terminal, Female, 0.76µm Gold (Au) Plating, Lubricated, 24-26 AWG	1053001400
Nano-Fit Crimp Terminal, Female,	1053002100

2.54µm Matte Tin
(Sn) Plating, 20-22
AWG
Nano-Fit Crimp 1053002200
Terminal, Female,
0.38µm Gold (Au)
Plating, 20-22 AWG
Nano-Fit Crimp 1053002300
Terminal, Female,
0.76µm Gold (Au)
Plating, 20-22 AWG
Nano-Fit Crimp 1053002400
Terminal, Female,
0.76µm Gold (Au)
Plating, Lubricated,
20-22 AWG
Nano-Fit Receptacle 1053071202
Housing, TPA
Capable, 2.50mm
Pitch, Single Row, 2
Circuits, Black, Glow-
Wire Capable
Nano-Fit Receptacle 1053071203
Housing, TPA
Capable, 2.50mm
Pitch, Single Row, 3
Circuits, Black, Glow-
Wire Capable
Nano-Fit Receptacle 1053071204
Housing, TPA
Capable, 2.50mm
Pitch, Single Row, 4
Circuits, Black, Glow-
Wire Capable
Nano-Fit Receptacle 1053071205
Housing, TPA
Capable, 2.50mm
Pitch, Single Row, 5
Circuits, Black, Glow-
Wire Capable
Nano-Fit Receptacle 1053071206
Housing, TPA
Capable, 2.50mm
Pitch, Single Row, 6
Circuits, Black, Glow-
Wire Capable
Nano-Fit Receptacle 1053071207
Housing, TPA
Capable, 2.50mm
Pitch, Single Row, 7
Circuits, Black, Glow-
Wire Capable
Nano-Fit Receptacle 1053071208
Housing, TPA
Capable, 2.50mm
Pitch, Single Row, 8
Circuits, Black, Glow-
Wire Capable
Nano-Fit Receptacle 1053072202
Housing, TPA
Capable, 2.50mm
Pitch, Single Row,
2 Circuits, Natural,
Glow-Wire Capable

Nano-Fit Receptacle [1053072203](#)
Housing, TPA
Capable, 2.50mm
Pitch, Single Row,
3 Circuits, Natural,
Glow-Wire Capable
Nano-Fit Receptacle [1053072204](#)
Housing, TPA
Capable, 2.50mm
Pitch, Single Row,
4 Circuits, Natural,
Glow-Wire Capable
Nano-Fit Receptacle [1053072205](#)
Housing, TPA
Capable, 2.50mm
Pitch, Single Row,
5 Circuits, Natural,
Glow-Wire Capable
Nano-Fit Receptacle [1053072206](#)
Housing, TPA
Capable, 2.50mm
Pitch, Single Row,
6 Circuits, Natural,
Glow-Wire Capable
Nano-Fit Receptacle [1053072207](#)
Housing, TPA
Capable, 2.50mm
Pitch, Single Row,
7 Circuits, Natural,
Glow-Wire Capable
Nano-Fit Receptacle [1053072208](#)
Housing, TPA
Capable, 2.50mm
Pitch, Single Row,
8 Circuits, Natural,
Glow-Wire Capable
Nano-Fit Receptacle [1053081204](#)
Housing, TPA
Capable, 2.50mm
Pitch, Dual Row, 4
Circuits, Black, Glow-
Wire Capable
Nano-Fit Receptacle [1053081206](#)
Housing, TPA
Capable, 2.50mm
Pitch, Dual Row, 6
Circuits, Black, Glow-
Wire Capable
Nano-Fit Receptacle [1053081208](#)
Housing, TPA
Capable, 2.50mm
Pitch, Dual Row, 8
Circuits, Black, Glow-
Wire Capable
Nano-Fit Receptacle [1053082204](#)
Housing, TPA
Capable, 2.50mm
Pitch, Dual Row,
4 Circuits, Natural,
Glow-Wire Capable
Nano-Fit Receptacle [1053082206](#)
Housing, TPA
Capable, 2.50mm
Pitch, Dual Row,

6 Circuits, Natural,
Glow-Wire Capable
Nano-Fit Receptacle 1053082208
Housing, TPA
Capable, 2.50mm
Pitch, Dual Row,
8 Circuits, Natural,
Glow-Wire Capable

This document was generated on 03/03/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION