



242W042-12-0 Product Details




Share



Print



Email



Active

Molded Parts

242W042-12-0

242W042-12-0

TE Internal Number: 804574-000

Product Highlights View All

- BS-G-198-5-DD, DEF Std 59-97 Issue 3 Type DD, SAE AS I 81765/4
- Molded Part Type = Molded Boots
- Connector or Backshell Outside Diameter = 20.00 mm, 22.00 mm, 24.00 mm, 26.00 mm
- Wire/Cable Outside Diameter = 8.00 mm, 9.00 mm, 10.00 mm, 11.00 mm, 12.00 mm
- Molded Part Shape = 45°

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Feedback

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Molded Part Type	Molded Boots
Molded Part Shape	45°
Molded Part Lip	With Lip
Angle	45°
Adhesive Description	Adhesive Purchased Separately

Mechanical Attachment

Adhesive Pre-Coating	Without
----------------------	---------

Dimensions

Connector or Backshell Outside Diameter (mm [in])	20.00 [0.787], 22.00 [0.870], 24.00 [0.940], 26.00 [1.020]
Wire/Cable Outside Diameter (mm [in])	8.00 [0.310], 9.00 [0.350], 10.00 [0.390], 11.00 [0.430], 12.00 [0.470]

Housing Features

Material Systems Code	200
-----------------------	-----

Configuration Features

Material Code	12
---------------	----

Industry Standards

Government/Industry Qualification	No
Approved Standards	BS-G-198-5-DD, DEF Std 59-97 Issue 3 Type DD, SAE AS I 81765/4
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Environmental

Operating Temperature (°C)	-55 – +200
----------------------------	------------

Purchasing Information

Adhesive Code	S1255-04
---------------	----------

Other

Adhesive Options	S1125 Separate Adhesive, -75°C to +150°C (-103°F to +302°F), S1255-04 Separate Adhesive, -55°C to +200°C (-67°F to +392°F)
Brand	Raychem

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

Corporate Information

- About TE
- Investors
- News Room
- Supplier Portal
- Careers
- Terms & Conditions
- Privacy Policy
- Global Accessibility Statement

Quick Links

- Distributor Inventory
- Product Cross Reference
- Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat With Us
- Find a Phone Number
- Knowledge Base
- Manage Your Account

Keep Me Informed

