

Rail Mounted Clips

The Maxclip System
Find a Clip

- » Find a Sales Associate
- » Find a Distributor
- » Design Assistance

Check Distributor Stock

Enter a part number for pricing and availability.

go!

Application Info

[Installation Demo Video](#)

[Thermal Performance](#)

[Tabless Packages](#)

[Tin Plated Pins](#)

[Shock and Vibration Testing](#)

[Choosing a Clip](#)

[Interface material selection](#)

Please note that these clips are intended solely for use with Aavid Thermalloy **Max Clip Extrusion Profiles**.

Part Number: MAX01NG

Low force clip


RoHS  Compliant



Force: 22 N [4.9 lbs]

Width: 10 mm [0.39 in]

Thickness: 0.5 mm [0.02 in]



Part Number: MAX01-HNG

High force clip


RoHS  Compliant



Force: 80 N [18.0 lbs]

Width: 10 mm [0.39 in]

Thickness: 0.7 mm [0.03 in]



Part Number: MAX02NG

Standard force clip


RoHS  Compliant



Force: 35 N [7.9 lbs]

Width: 12 mm [0.47 in]

Thickness: 0.5 mm [0.02 in]



Part Number: MAX02-HNG

High force clip


RoHS  Compliant



Force: 60 N [13.5 lbs]

Width: 13 mm [0.51 in]

Thickness: 0.6 mm [0.02 in]



Part Number: MAX03NG

Standard force clip


RoHS  Compliant



Force: 45 N [10.1 lbs]

Width: 15 mm [0.59 in]

Thickness: 0.5 mm [0.02 in]



Part Number: MAX03-HNG

High force clip


RoHS  Compliant



Force: 80 N [18.0 lbs]

Width: 18 mm [0.71 in]

Thickness: 0.6 mm [0.02 in]



Part Number: MAX04NG

Standard force clip


RoHS  Compliant



Force: 60 N [13.5 lbs]

Width: 20 mm [0.79 in]

Thickness: 0.5 mm [0.02 in]



Part Number: MAX09NG

Short standard force clip


RoHS  Compliant



Force: 45 N [10.1 lbs]

Width: 10 mm [0.39 in]

Thickness: 0.5 mm [0.02 in]



Part Number: MAX10NG

Long standard force clip


RoHS  Compliant










Force: 40 N [9.0 lbs]

Width: 12 mm [0.47 in]

Thickness: 0.6 mm [0.02 in]



Part Number: MAX12NG Low force clip RoHS  Compliant  Product Change Notice	
Force: 25 N [5.6 lbs] Width: 6 mm [0.24 in] Thickness: 0.6 mm [0.02 in]	
Part Number: MAX11NG Extra long standard force clip RoHS  Compliant  Product Change Notice	
Force: 40 N [9.0 lbs] Width: 12 mm [0.47 in] Thickness: 0.6 mm [0.02 in]	
Part Number: MAX23NG High force clip for use with thick insulator RoHS  Compliant	
Force: 100 N [22.5 lbs] Width: 18 mm [0.71 in] Thickness: 0.6 mm [0.02 in]	
Part Number: MAX20NG Standard force clip for use with thick insulator RoHS  Compliant	
Force: 47 N [10.6 lbs] Width: 12 mm [0.47 in] Thickness: 0.6 mm [0.02 in]	
Part Number: MAX13NG Standard force clip with locating features RoHS  Compliant	
Force: 45 N [10.1 lbs] Width: 17 mm [0.67 in] Thickness: 0.5 mm [0.02 in]	
Part Number: MAX14NG Low force clip with locating features RoHS  Compliant	
Force: 20 N [4.5 lbs] Width: 13 mm [0.51 in] Thickness: 0.5 mm [0.02 in]	
Part Number: MAX16NG Standard force clip with locating features RoHS  Compliant	
Force: 45 N [10.1 lbs] Width: 17 mm [0.67 in] Thickness: 0.5 mm [0.02 in]	

Customer Assistance

- [Contact Us](#)
- [Get Design Assistance](#)
- [Find a Distributor](#)
- [Find a Sales Rep](#)
- [Request a Quote](#)
- [Placing an Order](#)
- [Terms and Conditions](#)
- [Returns](#)

Popular Products

- [Fans](#)
- [Extrusions](#)
- [Board Level](#)
- [Liquid Cooling](#)
- [Heat Pipe Technology](#)
- [Heat Sink Accessories](#)
- [Interface Materials](#)

Our Company

- [News and Events](#)
- [Management Team](#)
- [Worldwide Locations](#)
- [Directions to Headquarters](#)
- [Disclaimer](#)
- [Customer Survey](#)
- [Privacy Policy](#)

Connect with Aavid

Sign up for Aavid News & Alerts

Email Address

GO!

Like / Follow / Connect



© Copyright 2015 Aavid Thermalloy, LLC.