

Hand bench presses / pneumatic presses

Identification	Part No.	Drawing	Dimensions in mm
Hand bench press	09 99 000 0201		Technical characteristics Working stroke 25 mm Press force 15 kN max. Hole $\varnothing$ in the ram $\varnothing$ 10 mm Net weight approx. 23 kg
Pneumatic press 40 kN	09 99 000 0282		Technical characteristics Total stroke 48 mm Working stroke 0-6 mm Press force 40 kN max. Air pressure 6 bar Hole $\varnothing$ in the ram $\varnothing$ 10.01 mm Net weight 136 kg Power supply 110 V / 220 V AC
Adaptor for height compensation ¹⁾	09 99 000 0279		
Guide frame with base plate Standard type for pcb size x = 123,5 - 309,5 mm	09 99 000 0244		
Long type ²⁾ for pcb size x = 123,5 - 668,5 mm	09 99 000 0261		
Base plate	09 99 000 0255		

¹⁾ suitable for 09 99 000 0282 and all CPM machines
²⁾ not suitable for hand bench press