

Han GND module, female



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 14 001 3132 |
| Specification | Han GND module, female |
| HARTING eCatalogue | https://harting.com/09140013132 |

Identification

| | |
|----------|----------------------|
| Category | Inserts |
| Series | Han [®] GND |

Version

| | |
|--------------------|--|
| Termination method | Crimp termination Axial screw termination |
| Gender | Female |
| Number of contacts | 1 |
| Details | Please order contacts separately. |

Technical characteristics

| | |
|-------------------------|---------------------------|
| Conductor cross-section | 10 ... 35 mm ² |
| Wire outer diameter | ≤13 mm |
| Insulation resistance | >10 ¹⁰ Ω |
| Limiting temperature | -40 ... +125 °C |
| Mating cycles | ≥500 |

Material properties

| | |
|---|--------------------|
| Material (insert) | Polycarbonate (PC) |
| Colour (insert) | Yellow |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|-------------------------------------|
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Not contained |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) + A1 (2023-10) |
| Requirement set with Hazard Levels | R26 |

Specifications and approvals

| | |
|----------------|--------------------------|
| Specifications | IEC 60664-1 IEC 61984 |
| UL / CSA | UL 1977 ECBT2.E235076 |

Commercial data

| | |
|--------------------------------|---|
| Packaging size | 2 |
| Net weight | 9.333 g |
| Country of origin | Germany |
| European customs tariff number | 85366990 |
| GTIN | 5713140019393 |
| eCl@ss | 27440205 Contact insert for industrial connectors |
| ETIM | EC000438 |
| UNSPSC 24.0 | 39121522 |