

Product Summary

Device	BVDSS	RDS(ON) Max	Id TA = +25°C
Q1 N-Channel	100V	220mΩ @ VGS = 10V	1.7A
		260mΩ @ VGS = 4.5V	1.6A
Q2 P-Channel	-100V	250mΩ @ VGS = -10V	-1.7A
		300mΩ @ VGS = -4.5V	-1.6A

Description and Applications

This new generation MOSFET has been designed to minimize the on-state resistance (R_{DS(ON)}) yet maintain superior switching performance, making it ideal for high efficiency power management applications.




- DC-DC Converters
- Power Management Functions
- Backlighting

Features and Benefits

- 100% Unclamped Inductive Switch (UIS) Test in Production
- Low Input Capacitance
- Low On-Resistance
- Fast Switching Speed
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please [contact us](#) or your local Diodes representative.
<https://www.diodes.com/quality/product-definitions/>

Mechanical Data

- Package: SO-8
- Package Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections: See Diagram
- Terminals: Finish – Tin Finish Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 
- Weight: 0.074 grams (Approximate)




Ordering Information (Note 4)

Part Number	Package	Packing	
		Qty.	Carrier
DMC10H220LSD-13	SO-8	2,500	Tape & Reel

Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
4. For packaging details, go to our website at <https://www.diodes.com/design/support/packaging/diodes-packaging/>.

Marking Information



DMC10H220LSD

Document number: DS43379 Rev. 2 - 2

DII = Manufacturer's Marking
 C10H2SD = Product Type Marking Code
 YYWW = Date Code Marking
 YY = Year (ex: 21 = 2021)
 WW = Week (01 to 53)

Maximum Ratings (@ $T_A = +25^\circ\text{C}$, unless otherwise specified.)

Characteristic			Symbol	Q1	Q2	Unit
Drain-Source Voltage			V_{DSS}	100	-100	V
Gate-Source Voltage			V_{GSS}	± 20	± 20	V
Continuous Drain Current (Note 6) N-Channel: $V_{GS} = 10\text{V}$ P-Channel: $V_{GS} = -10\text{V}$	Steady State	$T_A = +25^\circ\text{C}$ $T_A = +70^\circ\text{C}$	I_D	1.7 1.4	-1.7 -1.4	A
Maximum Body Diode Forward Current (Note 6)			I_S	1.7	-1.7	A
Pulsed Drain Current (10 μs Pulse, Duty Cycle = 1%)			I_{DM}	9	-13	A
Avalanche Current, $L = 0.1\text{mH}$			I_{AS}	3.2	-11	A
Avalanche Energy, $L = 0.1\text{mH}$			E_{AS}	0.5	6	mJ

Thermal Characteristics (@ $T_A = +25^\circ\text{C}$, unless otherwise specified.)

Characteristic			Symbol	Value	Unit
Total Power Dissipation (Note 5)			P_D	1	W
Thermal Resistance, Junction to Ambient (Note 5)	Steady State		$R_{\theta JA}$	110	$^\circ\text{C}/\text{W}$
Total Power Dissipation (Note 6)			P_D	1.5	W
Thermal Resistance, Junction to Ambient (Note 6)	Steady State		$R_{\theta JA}$	80	$^\circ\text{C}/\text{W}$
Operating and Storage Temperature Range			T_J, T_{STG}	-55 to +150	$^\circ\text{C}$

Electrical Characteristics N-Channel Q1 (@ $T_A = +25^\circ\text{C}$, unless otherwise specified.)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 7)						
Drain-Source Breakdown Voltage	BV_{DSS}	100	—	—	V	$V_{GS} = 0\text{V}, I_D = 250\mu\text{A}$
Zero Gate Voltage Drain Current	I_{DSS}	—	—	1	μA	$V_{DS} = 100\text{V}, V_{GS} = 0\text{V}$
Gate-Source Leakage	I_{GSS}	—	—	± 100	nA	$V_{GS} = \pm 20\text{V}, V_{DS} = 0\text{V}$
ON CHARACTERISTICS (Note 7)						
Gate Threshold Voltage	$V_{GS(TH)}$	1	—	3	V	$V_{DS} = V_{GS}, I_D = 250\mu\text{A}$
Static Drain-Source On-Resistance	$R_{DS(ON)}$	—	170	220	$\text{m}\Omega$	$V_{GS} = 10\text{V}, I_D = 1.6\text{A}$
		—	210	260		$V_{GS} = 4.5\text{V}, I_D = 1.3\text{A}$
Diode Forward Voltage	V_{SD}	—	0.7	1.2	V	$V_{GS} = 0\text{V}, I_S = 1.1\text{A}$
DYNAMIC CHARACTERISTICS (Note 8)						
Input Capacitance	C_{iss}	—	340	—	pF	$V_{DS} = 50\text{V}, V_{GS} = 0\text{V}$ $f = 1\text{MHz}$
Output Capacitance	C_{oss}	—	18	—		
Reverse Transfer Capacitance	C_{rss}	—	12	—		
Gate Resistance	R_g	—	2.1	—	Ω	$V_{DS} = 0\text{V}, V_{GS} = 0\text{V}, f = 1\text{MHz}$
Total Gate Charge ($V_{GS} = 4.5\text{V}$)	Q_g	—	4.1	—	nC	$V_{DS} = 50\text{V}, I_D = 1.6\text{A}$
Total Gate Charge ($V_{GS} = 10\text{V}$)	Q_g	—	8.3	—		
Gate-Source Charge	Q_{gs}	—	1.5	—		
Gate-Drain Charge	Q_{gd}	—	2	—	ns	$V_{DS} = 50\text{V}, V_{GS} = 4.5\text{V}, R_G = 6.8\Omega, I_D = 1\text{A}$
Turn-On Delay Time	$t_{D(ON)}$	—	6.8	—		
Turn-On Rise Time	t_R	—	8.2	—		
Turn-Off Delay Time	$t_{D(OFF)}$	—	7.9	—		
Turn-Off Fall Time	t_F	—	3.6	—	ns	$I_F = 1.1\text{A}, di/dt = 100\text{A}/\mu\text{s}$
Body Diode Reverse Recovery Time	t_{RR}	—	17	—		
Body Diode Reverse Recovery Charge	Q_{RR}	—	9.8	—	nC	

Notes:

5. Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.
6. Device mounted on FR-4 substrate PC board, 2oz copper, with 1inch square copper plate.
7. Short duration pulse test used to minimize self-heating effect.
8. Guaranteed by design. Not subject to product testing.

Electrical Characteristics P-Channel Q2 (@ $T_A = +25^\circ\text{C}$, unless otherwise specified.)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 7)						
Drain-Source Breakdown Voltage	BV_{DSS}	-100	—	—	V	$\text{V}_{\text{GS}} = 0\text{V}$, $\text{I}_D = -250\mu\text{A}$
Zero Gate Voltage Drain Current	I_{DSS}	—	—	-1	μA	$\text{V}_{\text{DS}} = -100\text{V}$, $\text{V}_{\text{GS}} = 0\text{V}$
Gate-Source Leakage	I_{GSS}	—	—	± 100	nA	$\text{V}_{\text{GS}} = \pm 20\text{V}$, $\text{V}_{\text{DS}} = 0\text{V}$
ON CHARACTERISTICS (Note 7)						
Gate Threshold Voltage	$\text{V}_{\text{GS(TH)}}$	-1.0	—	-3.0	V	$\text{V}_{\text{DS}} = \text{V}_{\text{GS}}$, $\text{I}_D = -250\mu\text{A}$
Static Drain-Source On-Resistance	$\text{R}_{\text{DS(ON)}}$	—	200	250	$\text{m}\Omega$	$\text{V}_{\text{GS}} = -10\text{V}$, $\text{I}_D = -1\text{A}$
		—	210	300		$\text{V}_{\text{GS}} = -4.5\text{V}$, $\text{I}_D = -1\text{A}$
Diode Forward Voltage	V_{SD}	—	-0.9	-1.2	V	$\text{V}_{\text{GS}} = 0\text{V}$, $\text{I}_S = -1\text{A}$
DYNAMIC CHARACTERISTICS (Note 8)						
Input Capacitance	C_{iss}	—	1030	—	pF	$\text{V}_{\text{DS}} = -50\text{V}$, $\text{V}_{\text{GS}} = 0\text{V}$, $f = 1.0\text{MHz}$
Output Capacitance	C_{oss}	—	33	—		
Reverse Transfer Capacitance	C_{rss}	—	24	—		
Gate Resistance	R_g	—	13	—	Ω	$\text{V}_{\text{DS}} = 0\text{V}$, $\text{V}_{\text{GS}} = 0\text{V}$, $f = 1.0\text{MHz}$
Total Gate Charge ($\text{V}_{\text{GS}} = -4.5\text{V}$)	Q_g	—	8.4	—	nC	$\text{V}_{\text{DS}} = -60\text{V}$, $\text{I}_D = -1\text{A}$
Total Gate Charge ($\text{V}_{\text{GS}} = -10\text{V}$)	Q_g	—	17.5	—		
Gate-Source Charge	Q_{gs}	—	2.8	—		
Gate-Drain Charge	Q_{gd}	—	3.2	—		
Turn-On Delay Time	$\text{t}_{\text{D(ON)}}$	—	9.1	—	ns	$\text{V}_{\text{DD}} = -50\text{V}$, $\text{R}_g = 9.1\Omega$, $\text{I}_D = -1\text{A}$
Turn-On Rise Time	t_r	—	14.9	—		
Turn-Off Delay Time	$\text{t}_{\text{D(OFF)}}$	—	57.4	—		
Turn-Off Fall Time	t_f	—	34.4	—		
Body Diode Reverse Recovery Time	t_{RR}	—	25.2	—	ns	$\text{V}_{\text{GS}} = 0\text{V}$, $\text{I}_S = -1\text{A}$, $\text{di/dt} = 100\text{A}/\mu\text{s}$
Body Diode Reverse Recovery Charge	Q_{RR}	—	24.5	—	nC	$\text{V}_{\text{GS}} = 0\text{V}$, $\text{I}_S = -1\text{A}$, $\text{di/dt} = 100\text{A}/\mu\text{s}$

Notes: 7. Short duration pulse test used to minimize self-heating effect.

8. Guaranteed by design. Not subject to product testing.

N-Channel Q1




Figure 1. Typical Output Characteristic




Figure 2. Typical Transfer Characteristic




Figure 3. Typical On-Resistance vs. Drain Current and Gate Voltage




Figure 4. Typical Transfer Characteristic




Figure 5. Typical On-Resistance vs. Drain Current and Temperature




Figure 6. On-Resistance Variation with Temperature




Figure 7. On-Resistance Variation with Temperature




Figure 8. Gate Threshold Variation vs. Junction Temperature




Figure 9. Diode Forward Voltage vs. Current




Figure 10. Typical Junction Capacitance




Figure 11. Gate Charge




Figure 12. SOA, Safe Operation Area

P-Channel Q2




Figure 13. Typical Output Characteristic




Figure 14. Typical Transfer Characteristic




Figure 15. Typical On-Resistance vs. Drain Current and Gate Voltage




Figure 16. Typical Transfer Characteristic




Figure 17. Typical On-Resistance vs. Drain Current and Temperature




Figure 18. On-Resistance Variation with Temperature




Figure 19. On-Resistance Variation with Temperature




Figure 20. Gate Threshold Variation vs. Junction Temperature




Figure 21. Diode Forward Voltage vs. Current




Figure 22. Typical Junction Capacitance




Figure 23. Gate Charge




Figure 24. SOA, Safe Operation Area





Figure 25. Transient Thermal Resistance


Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.



Suggested Pad Layout

Please see <http://www.diodes.com/package-outlines.html> for the latest version.



IMPORTANT NOTICE

1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
5. Diodes products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2021 Diodes Incorporated

www.diodes.com