


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	N2	ECN-22-152118	05MAY2022	RK	CDS



AMP WIRE RANGE	E13288 Listed	LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED

1. WIRE INSULATION DIAMETER: Ø2.667[Ø.105] TO Ø3.810[Ø.150]
2. BODY MATERIAL THK: 0.787±0.051[.031±.002]
3. FINISH:
BODY & SLEEVE – TIN PLATE 0.00254[.000100] MIN EXT THK PER
ASTM B545 INSULATION COLOR – BLUE
4. NOTE DELETED
5. FOREIGN PRODUCTION ONLY
6. NOTE DELETED
7. MATERIAL:
BODY & SLEEVE – COPPER PER ASTM B152
INSULATION – PVC
8. STAMP AMP 16-14* APPROX AS SHOWN
9. APPLIES FROM EDGE OF METAL WIRE BARREL
TO CENTER OF STUD HOLE

5	100	LOOSE PIECE	31904
	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 12APR2022 LINGANATHAN P.	TE Connectivity			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 300V MAX	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK 12APR2022 SUVARNA, CHETHAN D				
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 1.04-2.62mm²[2,050-5,180] CIR MILS SOLID OR STRANDED		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± - FINISH	APVD 12APR2022 SUVARNA, CHETHAN D	NAME TERMINAL, RING TONGUE, PIDG, WIRE SIZE: 16-14 AWG			
FOR ORDER ENTRY	1-800-526-5142		MATERIAL		PRODUCT SPEC UL 486A-B	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
					APPLICATION SPEC 114-2157	A3	00779	C-31904	
					WEIGHT -				
					CUSTOMER DRAWING	SCALE	NTS	SHEET	1 OF 1
								REV	N2