







PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



LEAD FREE PART NUMBERS									
SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	F±0.08	Au	0.76μ	Au
09	30.81	24.99	16.96	16.79	10.96	D09P34A4G*00LF	D09P34A6G*00LF		
15	39.14	33.32	25.18	25.12	19.18	D15P34A4G*00LF	D15P34A6G*00LF		
25	53.03	47.04	39.12	38.84	33.12	D25P34A4G*00LF	D25P34A6G*00LF		
37	69.32	63.50	55.68	55.30	49.68	D37P34A4G*00LF	D37P34A6G*00LF		

L ---> øT=M3
X ---> øT=UNC 4-40

GENERAL CHARACTERISTICS AND ROHS INFORMATION:
SEE DRAWING C01-8646-0000

mat'l. code		surface		tolerance		projection		product family	
-		ISO 1302		ISO 406		ISO 1101		D-SUB	
ltr	ecn no	dr	date	tolerances unless otherwise specified		angles		MM	
E	ELX-I-21654	AB	2015-10-26	linear		.0±0.1		MALE DD WT FOOTPRINT 6.9	
F	ELX-I-43906	ACU	2022-01-11	.000±0.1		scale 2:1		STRAIGHT SOLDER TYPE	
				dr		MASSON		dwg no	
						engr ARUN JOHN		sheet 1 of 1	
						chr GREGAR MATHEW		size	
						appd SANOU P KURIAKOS		A3	
						Amphenol FCI		type	
								Product Customer Drawing	
sheet index	revision	sheet	1						