



Connection Data

Solid conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Strip length	5 ... 6 mm / 0.2 ... 0.24 inches

Physical data

Width	17.5 mm / 0.689 inches
Height	35 mm / 1.378 inches
Depth from upper-edge of DIN-rail	27.5 mm / 1.083 inches

Material data

Fire load	0 MJ
Weight	11.7 g

Environmental requirements

Protection type	IP20
-----------------	------

Commercial data

Product Group	6 (INTERFACE ELECTRONIC)
PU (SPU)	15 (1) pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454526382
Customs tariff number	85369010000

Product Classification

UNSPSC	39121410
eCl@ss 10.0	27-37-12-92
eCl@ss 9.0	27-37-92-16
ETIM 9.0	EC002024
ETIM 10.0	EC002584
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant,With Exemption
RoHS Exemption	7(a) 7(c)-I 7(c)-II

Approvals / Certificates

Approvals for hazardous areas



Approval	Standard	Certificate Name
ATEX TUEV Nord Cert GmbH	EN 60079	TUEV12ATEX106032X (Ex ec[iaGa] IIC T4 Gc, [Ex ia-Da] IIIC, [Ex iaMa] I)
IECEX TUEV Nord Cert GmbH	IEC 60079	IECEX TUN12.0039X (Ex ec[iaGa] IIC T4 Gc, [Ex ia-Da] IIIC, [Ex iaMa] I)

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 288-936	↓

Documentation

Instruction Leaflet			
Resistance coupling element	13.12.2024	pdf 288.73 KB	↓

CAD/CAE-Data

CAE data

EPLAN Data Portal
288-936



WSCAD Universe
288-936

