




Color: ■ red



Dimensions in mm

| Connection Data                     |  |                                     |
|-------------------------------------|--|-------------------------------------|
| Metric cross-section of the ferrule |  | 6 mm <sup>2</sup>                   |
| Strip length                        |  | 16 ... 17 mm / 0.63 ... 0.67 inches |
| Cross-section (AWG) of ferrule      |  | 8 AWG                               |

| Physical data                         |  |        |
|---------------------------------------|--|--------|
| Total length (L)                      |  | 22 mm  |
| Wall thickness of crimp sleeve (W2)   |  | 0.2 mm |
| Wall thickness (plastic collar W1)    |  | 0.4 mm |
| Crimp length (length of sleeve L1)    |  | 12 mm  |
| Inner diameter of plastic collar (D1) |  | 7.6 mm |
| Diameter crimp sleeve inside (D2)     |  | 4.5 mm |

| Mechanical data |  |                 |
|-----------------|--|-----------------|
| Plastic collar  |  | Standard collar |

| Material data |  |       |
|---------------|--|-------|
| Color         |  | red   |
| Weight        |  | 0.5 g |

|             |                      |
|-------------|----------------------|
| UNSPSC      | 39121405             |
| eCl@ss 10.0 | 27-40-02-01          |
| eCl@ss 9.0  | 27-40-02-01          |
| ETIM 9.0    | EC000005             |
| ETIM 10.0   | EC000005             |
| ECCN        | NO US CLASSIFICATION |

|                        |                         |
|------------------------|-------------------------|
| RoHS Compliance Status | Compliant, No Exemption |
|------------------------|-------------------------|

## Environmental Product Compliance


Environmental Product Compliance 216-209

| Bid Text |            |                 |                   |
|----------|------------|-----------------|-------------------|
| 216-209  | 19.02.2019 | xml<br>2.80 KB  | <a href="#">↓</a> |
| 216-209  | 11.09.2017 | doc<br>24.00 KB | <a href="#">↓</a> |

## CAD data

### 2D/3D Models 216-209

## Installation Notes



A perfect gas-tight crimp – both electrically and mechanically reliable