

## Duplex Multimode 62.5/125 Fiber Patch Cable (LC/LC), 25M (82 ft.)

MODEL NUMBER: N320-25M



### Highlights

- Manufactured from 62.5/125 duplex (Zipcord) fiber
- Insertion loss testing performed on every connector (0.2dB typical)

### System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with LC connectors

### Package Includes

- 25 Meter ( 80ft ) Duplex MMF Cable LC/LC 62.5/125 Micron Fiber

### Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 25 meters ( 80ft ) Connectors: LC connector on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

## Specifications

| OVERVIEW              |              |
|-----------------------|--------------|
| UPC Code              | 037332134912 |
| Technology            | Multimode    |
| Optical Mode          | OM1          |
| PHYSICAL              |              |
| Cable Jacket Color    | Orange       |
| Connector Color       | Gray         |
| Cable Jacket Material | LSZH         |
| Cable Jacket Rating   | OFNR         |

|                                      |                                 |
|--------------------------------------|---------------------------------|
| Clad Diameter (microns)              | 125                             |
| Core Diameter (microns)              | 62.5                            |
| Number of Fibers                     | 2                               |
| Cable Length (ft.)                   | 82                              |
| Cable Length (m)                     | 25.00                           |
| Cable Length (in.)                   | 984.3                           |
| Minimum Bend Radius                  | 20 mm (Dynamic); 10 mm (Static) |
| Shipping Dimensions (hwd / in.)      | 12.00 x 10.50 x 0.50            |
| Shipping Dimensions (hwd / cm)       | 30.48 x 26.67 x 1.27            |
| Shipping Weight (lbs.)               | 0.43                            |
| Shipping Weight (kg)                 | 0.20                            |
| Fiber Cable Length                   | 25M (82 ft)                     |
| <b>ENVIRONMENTAL</b>                 |                                 |
| Operating Temperature Range          | -4° to 140°F (-20° to 60°C)     |
| Storage Temperature Range            | -4° to 140°F (-20° to 60°C)     |
| Operating Humidity Range             | 5% to 85% RH, Non-Condensing    |
| Storage Humidity Range               | 35% to 65% RH, Non-Condensing   |
| <b>COMMUNICATIONS</b>                |                                 |
| Network Compatibility                | 1 Gbps (Gigabit); 10 Gbps       |
| Attenuation @ 850NM                  | 3.0 dB/km                       |
| Insertion Loss                       | 0.20 dB                         |
| <b>CONNECTIONS</b>                   |                                 |
| Side A - Connector 1                 | LC DUPLEX (MALE)                |
| Side B - Connector 1                 | LC DUPLEX (MALE)                |
| Endface Polish                       | PC                              |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                 |
| Push/Pull Tabs                       | No                              |
| Breakout                             | No                              |
| Trunk                                | No                              |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                                 |
| Product Compliance                   | RoHS; REACH                     |



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

| WARRANTY & SUPPORT                     |                           |
|----------------------------------------|---------------------------|
| Product Warranty Period<br>(Worldwide) | Lifetime limited warranty |



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.