



Part Number : [734151001](#)

Product Description : MMCX Jack, Right-Angle, PCB Receptacle, Through Hole, Brass Body, Gold (Au) Plated, Tray, 50 Ohms

Series Number : 73414

Status : Active

Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

[734151001_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)


[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73414
Description	MMCX Jack, Right-Angle, PCB Receptacle, Through Hole, Brass Body, Gold (Au) Plated, Tray, 50 Ohms
Application	RF
Product Name	MMCX
Style	PCB
Type	Microminiature
UPC	800755970708

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 170 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	0.436/g
Orientation	Right Angle

Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Through Hole
PCB Thickness - Recommended	2.79mm
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	2
Max-Temp	260

This document was generated on Apr 21, 2026