

YA28A7, Compression Terminal, AL, 2-Hole, AL9CU

By Burndy

Catalog # [YA28A7](#)

Aluminum Compression Terminal, 4/0 AWG AL, 2-Hole, 3/8" Stud, 1" Spacing, Filled with Oxide Inhibitor, End Cap, AL9CU



Features

- UL486A-486B Listed and CSA Certified
- Aluminum terminals are dual rated to accommodate both copper and aluminum wire and are indicated with AL-CU on the connector - AL9CU is UL Listed 90°C, up to 35kV, AL7CU is UL Listed 75°C, up to 35kV
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damage of the wire strands during insertion
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with wire size, die index, color code, and crimp location bands
- Factory pre-filled with PENETROX Type A13 oxide inhibitor
- Color coded end caps are factory inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel
- Aluminum oxidation is not easily detected but causes resistance in a connection, it is imperative the proper preparation takes place prior to making an aluminum-to-aluminum connection

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	ALUMINUM / COPPER
Wire Size	4/0 AWG
Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG

Conductor - Copper Str Size	4/0 AWG
Conductor Size	4/0 AWG
Conductor - Copper Solid Size	4/0 AWG
Conductor - Copper Solid Size Range	4/0 AWG
Conductor Type	CODE
Conductor - Copper Str Size Range	4/0 AWG

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	DUAL RATED

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.17 in
Package Height	3.400 in
Dimension - Hole Size fraction	3/8
Package Weight	1.480 lb.
Package Length	7.550 in
Package Width	4.950 in
Dimension - L Length Overall mm	101 mm
Dimension - Outside Diameter inch	0.85 in
Dimension - Thread Size	3/8
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1-5/8
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-3/8 in
Dimension - Z inch	0.45 in
Dimension - B Length inch	1.39 in
Dimension - D inch	1.89 in
Dimension - N inch	0.44 in
Dimension - Bolt Size inch	0.38

Dimension - Length Overall inch	3.97 in	Finish Type	Tin-Plated
		UPC 12 Digit	781810023464
		UPC 14 Digit GTIN	00781810023464
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	10
Die Index	298	Pallet Quantity	3840
Feature - Barrel Type	Standard	Carton Quantity	60
Feature - Barrel Style	Chamfered		
Plated	Y	Operational	
Color Code	White	Temperature Rating	194
Physical Attribute - Tongue Type	Standard		
Sub Brand	HYLUG	Product Assets	
UPC	781810023464	Catalog [English]	
Type	YA-A, Dual Rated	Installation Manual [English]	
Material	Aluminum	Installation Manual [English]	
Plating Type	Tin - Electro Plated		



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-YA28A7-SPEC-EN | REV 5/2026