





PRODUCT DESCRIPTION CODE :

10145028-0XX LF


- ROHS COMPATIBLE
- FOR CUSTOMER CODE :
BLANK = GENERAL USE
- PACKAGING :
BLANK = BULK
- BLANK = WITH CPA
W = WITHOUT CPA
- NUMBER OF POSITIONS : 14 TO 30

NOTES:

- MATERIAL:
HIGH TEMPERATURE THERMOPLASTIC
COLOR BLACK UL94 V-0
- FOR USE WITH MINITEK μ SPACE CTW TERMINALS :
AWG 28-30, SERIES 10141272 & 10148496
- TO BE MATED WITH MINITEK μ SPACE HEADERS SERIES
10145030 / 10145204
- THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO ANY
SOLDER PROCESS.
- ROHS COMPATIBLE PRODUCT SPECIFICATIONS
 - LABELLING :
MEETS PACKAGING SPECS AS PER GS-14-920
 - LEGAL STATEMENT :
SEE GS-47-0004.




10145028-0XXLF (WITH CPA)



10145028-0XXWLF (WITHOUT CPA)

PRE-LOAD CONFIGURATION : DELIVERED STATUS


spec ref -				dr	Sawanth, Ambaa	2018/11/01	projection 	mm 	size	A3	scale	4:1
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Canque, Vincen	2021/07/28			ecn no	ELX-F-41845-1		
				chr	-	-			rel level Released			
				appr	Cyril Jeune	2021/07/29						
surface ISO 1302	linear	0.X	±0.3	Amphenol FCI	title RECEPTACLE ASSEMBLY MINITEK μSPACE STS DR 1.27 TOP LATCH				dwg no	10145028		rev B
		0.XX	±0.10									
		0.XXX	±0.005									
		angular	0°	±2°		cat. no.	-	Product - Customer Drw			sheet 1 of 3	

PRE-LOAD CONFIGURATION FOR TERMINAL INSERTION


FINAL LOAD CONFIGURATION WITH INSERTED TERMINAL

FULL HEADER AND RECEPTACLE ASSEMBLY CONFIGURATION


PART NO	NO.OF POSN	DIM "A"
10145028-014LF	14	11.48
10145028-016LF	16	12.75
10145028-018LF	18	14.02
10145028-020LF	20	15.29
10145028-022LF	22	16.56
10145028-024LF	24	17.83
10145028-026LF	26	19.10
10145028-028LF	28	20.37
10145028-030LF	30	21.64



spec ref -				dr		Sawanth, Ambaa		2018/11/01		projection		mm		size		A3		scale		3:1			
tolerance std				eng		Canque, Vincen		2021/07/28						ecn no		ELX-F-41845-1							
ISO 406				chr		-		-								rel level							
ISO 1101				appr		Cyril Jeune		2021/07/29														product family	
TOLERANCES UNLESS OTHERWISE SPECIFIED																							
surface				linear		0.X		±0.3		Amphenol FCI		title		RECEPTACLE ASSEMBLY		dwg no		10145028		rev		B	
						0.XX		±0.10															
						0.XXX		±0.005															
ISO 1302				angular		0°		±2°				cat. no.		-		Product - Customer Drw		sheet 2 of 3					




TEST PROBE $\varnothing 0.4\text{mm}$ COMPLIANCE




HOLE FOR TEST PROBE

DETAIL A
SCALE 20:1



RECOMMENDED LAYOUT OF TEST PROBE $\varnothing 0.4\text{mm}$

spec ref -				dr Sawanth, Ambaa		2018/11/01				size A3		scale 8:1							
tolerance std				eng Canque, Vincen		2021/07/28				ecn no ELX-F-41845-1									
ISO 406				chr -		-				rel level Released									
ISO 1101				appr Cyril Jeune		2021/07/29				product family -									
surface  ISO 1302		linear		0.X		±0.3				title RECEPTACLE ASSEMBLY				dwg no 10145028		rev B			
				0.XX		±0.10													
				0.XXX		±0.005													
				angular		0°		±2°				cat. no. -				Product - Customer Drw			