




Home> Products > MICRO SWITCH™ Toggle Switches> TL > Product Page

102TL2259-7



Actual product appearance may vary.

TL Series Toggle Switch, 2 pole, 3 position, IWTS (16 -20 Gage) terminal, Paddle Lever

Features

- Environmentproof sealing
- 1,2, and 4 pole circuitry
- Standard and pull-to-unlock levers
- 2 and 3 position, maintained and momentary toggle action
- Temperature range: -85° F to +160° F
- Completely sealed switching chamber
- Step-design case provides added space between terminals to help prevent shorting
- UL recognized, CSA certified
- CE approved

Potential Applications

- Industrial machinery and equipment
- Military and commercial aviation
- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

Description

MICRO SWITCH™TL Series toggle switches have high strength, temperature resistant, non-tracking case material and silver cadmium oxide contacts. Pull-to-Unlock toggle levers prevent accidental operation; the lever must be pulled approx. 2,3 mm (0.09 inches) to change positions.

Supporting Documentation

- [Accessory: Lever Sleeve](#)
- [Accessory: Seals](#)
- [Accessory: Nuts](#)
- [Engineering Drawing](#)

Product Specifications			
Circuitry/Operating action	<b>Keyway</b>		<b>Opposite Keyway</b>
	<b>Momentary Position</b>	<b>Center Position</b>	<b>Momentary Position</b>
	ON	OFF	ON
Product Type	MICRO SWITCH™ Toggle Switch		
Ampere/Voltage Range (Resistive Load)	0.75 A at 115 Vdc,0.5 A at 250 Vdc,0.5 A to 6 A at 0.5 Vac to 230 Vac,0.5 A to 7.5 A at 0.5 Vdc to 28 Vdc		
Circuitry	DPDT		
Action	3 position		
Mounting	Bushing 15/32 in		
Termination	IWTS (16 - 20 Gage)		
Lever Type	Paddle		
Comment	100% immersion test per QS 047 287, paddle marking (Program - Off - Escape), black anodized aluminum lever		
Availability	Global		
UNSPSC Code	30211908		
UNSPSC Commodity	30211908 Toggle switches		
Series Name	TL		

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (\*) to expand search

Specification Search