

C3216X7R2J103K115AM

TDK Item Description : C3216X7R2J103KT5***



Application & Main Feature

Commercial Grade (Open Mode)

Series

C3216 [EIA CC1206]

Dimensions

L 3.20mm +/-0.2mm
W 1.60mm +/-0.2mm
T 1.15mm +/-0.15mm
B 0.20mm Min.
G 1.00mm Min.

Temperature Characteristic

X7R (-55 to 125 degC +/-15%)

Rated Voltage

2J (630Vdc)

Capacitance

10nF

Capacitance Tolerance

K (+/-10%)

Dissipation Factor


3% Max.

Insulation Resistance


10Gohm Min.

AEC-Q200


Not Applicable




DC Bias Characteristic




|Z|, ESR vs. Freq. Characteristics




Temperature Characteristics



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristics



All specifications are subject to change without notice.

January 3, 2016