

Final datasheet

IHM-B module with Trench/Fieldstop IGBT4 and emitter controlled 4 diode

Features

- Electrical features
 - $V_{CES} = 3300\text{ V}$
 - $I_{C\text{ nom}} = 1200\text{ A} / I_{CRM} = 2400\text{ A}$
 - High current density
 - High DC stability
 - High short-circuit capability
 - Low switching losses
 - Low $V_{CE,sat}$
 - $T_{vj,op} = 150^{\circ}\text{C}$
 - Trench IGBT 4
 - Unbeatable robustness
 - $V_{CE,sat}$ with positive temperature coefficient
 - Low Q_g and C_{res}
- Mechanical features
 - ALSiC base plate for increased thermal cycling capability
 - High power density
 - Isolated base plate
 - Package with CTI > 600
 - RoHS compliant



Typical appearance

Potential applications

- High-power converters
- Medium-voltage converters
- Motor drives
- Traction drives
- UPS systems
- Active frontend (energy recovery)

Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068

Description






Table of contents

	Description	1
	Features	1
	Potential applications	1
	Product validation	1
	Table of contents	2
1	Package	3
2	IGBT, Inverter	3
3	Diode, Inverter	5
4	Characteristics diagrams	7
5	Circuit diagram	11
6	Package outlines	11
7	Module label code	12
	Revision history	13
	Disclaimer	14

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, $f = 50$ Hz	6.0	kV
Partial discharge extinction voltage	V_{isol}	RMS, $f = 50$ Hz, $Q_{PD} \leq 10$ pC	2.6	kV
DC stability	$V_{CE(D)}$	$T_{vj} = 25$ °C, 100 Fit	2100	V
Material of module baseplate			AlSiC	
Creepage distance	$d_{Creep\ nom}$	terminal to baseplate, nom.	32.2	mm
Clearance	$d_{Clear\ nom}$	terminal to baseplate, nom.	19.1	mm
Comparative tracking index	CTI		> 600	

Table 2 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Stray inductance module	L_{sCE}				6		nH
Module lead resistance, terminals - chip	$R_{AA'+CC'}$	T _C = 25 °C, per switch			0.08		mΩ
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	T _C = 25 °C, per switch			0.14		mΩ
Storage temperature	T_{stg}			-40		150	°C
Mounting torque for module mounting	M	- Mounting according to valid application note	M6, Screw	4.25		5.75	Nm
Terminal connection torque	M	- Mounting according to valid application note	M4, Screw	1.8		2.1	Nm
			M8, Screw	8		10	
Weight	G				1200		g

2 IGBT, Inverter

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Collector-emitter voltage	V_{CES}		$T_{vj} = -40$ °C	3300	V
			$T_{vj} = 150$ °C	3300	
Continuous DC collector current	I_{CDC}	$T_{vj\ max} = 150$ °C	$T_C = 105$ °C	1200	A
Repetitive peak collector current	I_{CRM}	t_p limited by $T_{vj\ op}$		2400	A
Gate-emitter peak voltage	V_{GES}			±20	V

Table 4 **Characteristic values**

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CE\ sat}$	$I_C = 1200\ A, V_{GE} = 15\ V$	$T_{vj} = 25\ ^\circ C$		2.40	2.65	V
			$T_{vj} = 125\ ^\circ C$		2.95		
			$T_{vj} = 150\ ^\circ C$		3.10	3.25	
Gate threshold voltage	V_{GETh}	$I_C = 47\ mA, V_{CE} = V_{GE}, T_{vj} = 25\ ^\circ C$		5.20	5.80	6.40	V
Gate charge	Q_G	$V_{GE} = \pm 15\ V, V_{CC} = 1800\ V$			20		μC
Internal gate resistor	R_{Gint}	$T_{vj} = 25\ ^\circ C$			1		Ω
Input capacitance	C_{ies}	$f = 1000\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$			140		nF
Reverse transfer capacitance	C_{res}	$f = 1000\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$			4		nF
Collector-emitter cut-off current	I_{CES}	$V_{CE} = 3300\ V, V_{GE} = 0\ V$	$T_{vj} = 25\ ^\circ C$			5	mA
Gate-emitter leakage current	I_{GES}	$V_{CE} = 0\ V, V_{GE} = 20\ V, T_{vj} = 25\ ^\circ C$				400	nA
Turn-on delay time (inductive load)	t_{don}	$I_C = 1200\ A, V_{CC} = 1800\ V, V_{GE} = \pm 15\ V, R_{Gon} = 1.2\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.540		μs
			$T_{vj} = 125\ ^\circ C$		0.670		
			$T_{vj} = 150\ ^\circ C$		0.700		
Rise time (inductive load)	t_r	$I_C = 1200\ A, V_{CC} = 1800\ V, V_{GE} = \pm 15\ V, R_{Gon} = 1.2\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.210		μs
			$T_{vj} = 125\ ^\circ C$		0.230		
			$T_{vj} = 150\ ^\circ C$		0.230		
Turn-off delay time (inductive load)	t_{doff}	$I_C = 1200\ A, V_{CC} = 1800\ V, V_{GE} = \pm 15\ V, R_{Goff} = 6.2\ \Omega$	$T_{vj} = 25\ ^\circ C$		3.900		μs
			$T_{vj} = 125\ ^\circ C$		4.200		
			$T_{vj} = 150\ ^\circ C$		4.300		
Fall time (inductive load)	t_f	$I_C = 1200\ A, V_{CC} = 1800\ V, V_{GE} = \pm 15\ V, R_{Goff} = 6.2\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.800		μs
			$T_{vj} = 125\ ^\circ C$		1.400		
			$T_{vj} = 150\ ^\circ C$		1.500		
Turn-on time (resistive load)	t_{on_R}	$I_C = 500\ A, V_{CC} = 2000\ V, V_{GE} = \pm 15\ V, R_{Gon} = 1.2\ \Omega$	$T_{vj} = 25\ ^\circ C$	1.20			μs
Turn-on energy loss per pulse	E_{on}	$I_C = 1200\ A, V_{CC} = 1800\ V, L_\sigma = 85\ nH, V_{GE} = \pm 15\ V, R_{Gon} = 1.2\ \Omega, di/dt = 4400\ A/\mu s (T_{vj} = 150\ ^\circ C)$	$T_{vj} = 25\ ^\circ C$		1680		mJ
			$T_{vj} = 125\ ^\circ C$		2490		
			$T_{vj} = 150\ ^\circ C$		2750		
Turn-off energy loss per pulse	E_{off}	$I_C = 1200\ A, V_{CC} = 1800\ V, L_\sigma = 85\ nH, V_{GE} = \pm 15\ V, R_{Goff} = 6.2\ \Omega, dv/dt = 1450\ V/\mu s (T_{vj} = 150\ ^\circ C)$	$T_{vj} = 25\ ^\circ C$		1760		mJ
			$T_{vj} = 125\ ^\circ C$		2320		
			$T_{vj} = 150\ ^\circ C$		2490		

(table continues...)

Table 4 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
SC data	I_{SC}	$V_{GE} \leq 15 \text{ V}$, $V_{CC} = 2400 \text{ V}$, $V_{CEmax} = V_{CES} - L_{SCE} \cdot di/dt$ $t_p \leq 10 \mu\text{s}$, $T_{vj} \leq 150 \text{ }^\circ\text{C}$		5200		A
Thermal resistance, junction to case	R_{thJC}	per IGBT			11.9	K/kW
Thermal resistance, case to heat sink	R_{thCH}	per IGBT, $\lambda_{grease} = 1 \text{ W/(m}\cdot\text{K)}$		4.70		K/kW
Temperature under switching conditions	$T_{vj op}$		-40		150	$^\circ\text{C}$

3 Diode, Inverter

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Repetitive peak reverse voltage	V_{RRM}		$T_{vj} = -40 \text{ }^\circ\text{C}$	3300	V
			$T_{vj} = 150 \text{ }^\circ\text{C}$	3300	
Continuous DC forward current	I_F			1200	A
Repetitive peak forward current	I_{FRM}	$t_p = 1 \text{ ms}$		2400	A
I^2t - value	I^2t	$t_p = 10 \text{ ms}$, $V_R = 0 \text{ V}$	$T_{vj} = 125 \text{ }^\circ\text{C}$	630	kA^2s
			$T_{vj} = 150 \text{ }^\circ\text{C}$	570	
Maximum power dissipation	P_{RQM}		$T_{vj} = 150 \text{ }^\circ\text{C}$	3600	kW
Minimum turn-on time	t_{onmin}			10	μs

Table 6 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 1200 \text{ A}$, $V_{GE} = 0 \text{ V}$	$T_{vj} = 25 \text{ }^\circ\text{C}$	2.60	3.00	V
			$T_{vj} = 125 \text{ }^\circ\text{C}$	2.30		
			$T_{vj} = 150 \text{ }^\circ\text{C}$	2.20	2.50	
Peak reverse recovery current	I_{RM}	$V_{CC} = 1800 \text{ V}$, $I_F = 1200 \text{ A}$, $V_{GE} = -15 \text{ V}$, $-di_F/dt = 4400 \text{ A}/\mu\text{s}$ ($T_{vj} = 150 \text{ }^\circ\text{C}$)	$T_{vj} = 25 \text{ }^\circ\text{C}$	1280		A
			$T_{vj} = 125 \text{ }^\circ\text{C}$	1460		
			$T_{vj} = 150 \text{ }^\circ\text{C}$	1520		

(table continues...)

Table 6 (continued) Characteristic values


Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Recovered charge	Q_r	$V_{CC} = 1800 \text{ V}$, $I_F = 1200 \text{ A}$, $V_{GE} = -15 \text{ V}$, $-di_F/dt = 4400 \text{ A}/\mu\text{s}$ ($T_{vj} = 150 \text{ }^\circ\text{C}$)	$T_{vj} = 25 \text{ }^\circ\text{C}$	585		μC
			$T_{vj} = 125 \text{ }^\circ\text{C}$	1150		
			$T_{vj} = 150 \text{ }^\circ\text{C}$	1350		
Reverse recovery energy	E_{rec}	$V_{CC} = 1800 \text{ V}$, $I_F = 1200 \text{ A}$, $V_{GE} = -15 \text{ V}$, $-di_F/dt = 4400 \text{ A}/\mu\text{s}$ ($T_{vj} = 150 \text{ }^\circ\text{C}$)	$T_{vj} = 25 \text{ }^\circ\text{C}$	545		mJ
			$T_{vj} = 125 \text{ }^\circ\text{C}$	1230		
			$T_{vj} = 150 \text{ }^\circ\text{C}$	1460		
Thermal resistance, junction to case	R_{thJC}	per diode			16.7	K/kW
Thermal resistance, case to heat sink	R_{thCH}	per diode, $\lambda_{grease} = 1 \text{ W}/(\text{m}\cdot\text{K})$		6.45		K/kW
Temperature under switching conditions	$T_{vj op}$		-40		150	$^\circ\text{C}$

4 Characteristics diagrams

Output characteristic (typical), IGBT, Inverter

$I_C = f(V_{CE})$


$V_{GE} = 15\text{ V}$



Output characteristic field (typical), IGBT, Inverter

$I_C = f(V_{CE})$


$T_{vj} = 150\text{ °C}$



Transfer characteristic (typical), IGBT, Inverter

$I_C = f(V_{GE})$


$V_{CE} = 20\text{ V}$



Gate charge characteristic (typical), IGBT, Inverter

$V_{GE} = f(Q_G)$


$I_C = 1200\text{ A}, T_{vj} = 25\text{ °C}$



4 Characteristics diagrams


Capacity characteristic (typical), IGBT, Inverter

$C = f(V_{CE})$
 $f = 100\text{ kHz}$, $V_{GE} = 0\text{ V}$, $T_{vj} = 25\text{ }^{\circ}\text{C}$




Switching times (typical), IGBT, Inverter

$t = f(I_C)$
 $R_{Goff} = 6.2\text{ }\Omega$, $R_{Gon} = 1.2\text{ }\Omega$, $V_{CC} = 1800\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $T_{vj} = 150\text{ }^{\circ}\text{C}$




Switching times (typical), IGBT, Inverter

$t = f(R_G)$
 $I_C = 1200\text{ A}$, $V_{CC} = 1800\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $T_{vj} = 150\text{ }^{\circ}\text{C}$



Switching losses (typical), IGBT, Inverter


$E = f(I_C)$
 $R_{Goff} = 6.2\text{ }\Omega$, $R_{Gon} = 1.2\text{ }\Omega$, $V_{CC} = 1800\text{ V}$, $V_{GE} = \pm 15\text{ V}$



4 Characteristics diagrams


Switching losses (typical), IGBT, Inverter

$E = f(R_G)$
 $I_C = 1200\text{ A}$, $V_{CC} = 1800\text{ V}$, $V_{GE} = \pm 15\text{ V}$




Reverse bias safe operating area (RBSOA), IGBT, Inverter

$I_C = f(V_{CE})$
 $R_{Goff} = 6.2\ \Omega$, $V_{GE} = 15\text{ V}$, $T_{vj} = 150\text{ °C}$




Transient thermal impedance, IGBT, Inverter

$Z_{th} = f(t)$



Forward characteristic (typical), Diode, Inverter


$I_F = f(V_F)$



4 Characteristics diagrams


Switching losses (typical), Diode, Inverter

$E_{rec} = f(I_F)$
 $V_{CE} = 1800\text{ V}, R_{Gon} = R_{Gon}(IGBT)$




Switching losses (typical), Diode, Inverter

$E_{rec} = f(R_G)$
 $V_{CE} = 1800\text{ V}, I_F = 1200\text{ A}$




Safe operating area (SOA), Diode, Inverter

$I_R = f(V_R)$
 $T_{vj} = 150\text{ }^\circ\text{C}$



Transient thermal impedance, Diode, Inverter

$Z_{th} = f(t)$



5 Circuit diagram




Figure 1

6 Package outlines




Figure 2

7 Module label code

Module label code			
Code format	Data Matrix		Barcode Code128
Encoding	ASCII text		Code Set A
Symbol size	16x16		23 digits
Standard	IEC24720 and IEC16022		IEC8859-1
Code content	<i>Content</i>	<i>Digit</i>	<i>Example</i>
	Module serial number	1 – 5	71549
	Module material number	6 - 11	142846
	Production order number	12 - 19	55054991
	Date code (production year)	20 – 21	15
	Date code (production week)	22 – 23	30
Example			
			
71549142846550549911530		71549142846550549911530	

Figure 3



Revision history

Revision history

Document revision	Date of release	Description of changes
0.10	2024-03-18	Initial version
1.00	2024-04-30	Final datasheet

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2024-04-30

Published by

Infineon Technologies AG
81726 Munich, Germany

© 2024 Infineon Technologies AG
All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-ABJ734-002

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Please note that this product is not qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.