

3125A Multi-Conductor - DeviceBus® for Square D/Seriplex®



For more Information
please call

1-800-Belden1



Description

16 and 22 AWG stranded tinned copper conductors, foam HDPE insulation (power), foam HDPE insulation (data), overall Beldfoil® shield (100% coverage), 22 AWG stranded (7x30) tinned copper drain wire, PVC jacket.

Physical Characteristics (Overall):

Conductor:

AWG

# Conductors	AWG	Stranding	Conductor Material	Dia. (in.)
2	16	26x30	TC - Tinned Copper	0.060
2	22	7x30	TC - Tinned Copper	0.030

Insulation:

Insulation Material

Layer #	Ins Trade Name	Ins Material	Wall Thickness (in.)	Dia. (in.)	AWG
		FHDPE - Foam High Density Polyethylene	0.025		16
		FHDPE - Foam High Density Polyethylene	0.040		22

Outer Shield:

Outer Shield Material

Outer Shield Trade Name	Type	Outer Shield Material
Beldfoil®	Tape	Aluminum Foil-Polyester Tape

Outer Shield Drain Wire AWG

AWG	Stranding	Drain Wire Conductor Material
22	7x30	TC - Tinned Copper

Outer Shield Drain Wire Diameter .030

Outer Jacket:

Outer Jacket Material

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cabling:

Overall Cabling Lay Length & Direction

Length (in.)	Direction
4.000	Left Hand

Overall Cabling Separator Material Foamed Polypropylene Tape

Overall Nominal Diameter: .368 in.

Mechanical Characteristics (Overall):

Operating Temperature Range -20°C To +75°C

Non-UL Temperature Rating 75°C

Bulk Cable Weight: 55.600 lbs/1000 ft.

Max. Recommended Pulling Tension: 85 lbs.

Applicable Specifications and Agency Compliance (Overall):

Applicable Standards:

NEC/(UL) Specification CL2, CM

3125A Multi-Conductor - DeviceBus® for Square D/Seriplex®

CEC/C(UL) Specification	CM
EU CE Mark (Y/N)	Yes
EU RoHS Compliant (Y/N)	Yes
EU RoHS Compliance Date (mm/dd/yyyy)	01/01/2004
Other Specification	Seriplex CBL 1622-P1
Flame Test:	
UL Flame Test	UL1685 UL Loading
Plenum/Non-Plenum:	
Plenum (Y/N)	N

Electrical Characteristics (Overall):

Nom. Capacitance Conductor to Shield

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Capacitance (pF/ft)
22 AWG				16.000
16 AWG				28.000

Nom. Capacitance Conductor to Conductor

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Capacitance (pF/ft)
22 AWG				9.000
16 AWG				16.000

Nominal Velocity of Propagation

Description	VP (%)
16 AWG	78
22 AWG	78

Nom. Conductor DC Resistance

Description	DCR @ 20°C (Ohm/1000 ft)
16 AWG	4.490
22 AWG	18.100

Nominal Outer Shield DC Resistance

DCR @ 20°C (Ohm/1000 ft)
16.000

Max. Operating Voltage - UL

Voltage	Description
300 V RMS	CM
150 V RMS	CL2

Max. Operating Voltage - Non-UL

Voltage
350 V RMS

PUT UPS AND COLORS:

Item #	Putup	Ship Weight	Jacket Color	Notes	Item Desc
3125A 0031000	1,000 FT	63.000 LB	ORANGE	C	2 #16,2#22 FHDPE FS PVC ORG
3125A 003500	500 FT	31.500 LB	ORANGE	C	2 #16,2#22 FHDPE FS PVC ORG

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 05-14-2007

3125A Multi-Conductor - DeviceBus® for Square D/Seriplex®

© 2007 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with the following environmental regulations: California Proposition 65 Consent Judgment For Wire & Cable Mfgs.(San Francisco Superior Court Nos. 312962 And 320342); EU RoHS (Directive 2002/95/EC, 27-Jan-2003); Material manufactured prior to the compliance date may still be in stock at Belden facilities and in our Distributor's inventory; and China Ministry of Information Industry order#39 (China RoHS). EU ELV (Directive 2000/53/EC, 18-Sept-2000); EU WEEE (Directive 2002/96/EC, 27-Jan-2003); EU BFR (Directive 2003/11/EC, 6-Feb-2003). The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information and belief at the date of its publication. The information provided in the Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.