Part Number : 1200710047
Product Description : M12 Signal, A-Coded, Field-Attachable, 5 Poles, Male, Straight, PG9 Gland, 4.10-8.10mm
Series Number : 120071
Status : Active
Product Category : Circular Industrial Connectors
Engineering Part Number : 8A5006-32



Documents and Resources

Drawings

1200710047_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025) SCIP:305b3d53-3273-4db4-a8d7-43bea26240cc
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120071
Description	M12 Signal, A-Coded, Field-Attachable, 5 Poles, Male, Straight, PG9 Gland, 4.10-8.10mm
Approvals	cCSAus certified
IP Rating	IP67
Product Name	M12 Signal,Micro-Change (M12)
Type	Field Attachable Connector
UPC	78172553221

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	30V AC / 36V DC

Physical

Cable Diameter	4.10-8.10mm (.161-.319")
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	A-Coded
Material - Connector Body	PA

Downloaded from Arrow.com.

Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Silver
Net Weight	29.000/g
Orientation	Straight
Poles	5
Temperature Range - Operating	-25° to +90°C
Wire Size (AWG)	18

Downloaded from Arrow.com.