



**Part Number :** [1200878038](#)

**Product Description :** Nano-Change (M8) to Micro-Change (M12) Double-Ended Cordset, 3 Poles, Female (Straight) to Male (Straight), 0.25mm<sup>2</sup> PVC Cable, 0.60m (1.97') Length

**Series Number :** 120087

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 483030E02M006



---

## Documents and Resources


### Drawings

[1200878038\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:355989a7-ce24-49dd-a805-426703ce21d9
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	120087
Description	Nano-Change (M8) to Micro-Change (M12) Double-Ended Cordset, 3 Poles, Female (Straight) to Male (Straight), 0.25mm <sup>2</sup> PVC Cable, 0.60m (1.97') Length
IP Rating	IP68
Product Name	Micro-Change (M12), Nano-Change (M8)
Protocol	N/A
Type	Double Ended
UPC	883906364359

### Agency

UL	E152210
----	---------

### Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC

### Physical

Cable Diameter	N/A
----------------	-----

Cable Length	0.60m (1.97')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	None
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPU
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	44.137/g
Orientation	Straight to Straight
Poles	3
Temperature Range - Operating	-30° to +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	N/A

---

This document was generated on Apr 22, 2026