

SK2291

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO POSITRONIC AND IT'S SUBSIDIARIES. POSITRONIC BELIEVES THE DATA ON THIS DRAWING TO BE RELIABLE, SINCE THE TECHNICAL INFORMATION IS GIVEN FREE OF CHARGE, THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.

DATE	REV	REVISION RECORD	APP	DR	CK
9-6 01	A	ECO 18276		ME	





NOTES:
1. MATERIALS AND FINISHES:
   INSULATOR: GLASS FILLED POLYESTER, UL 94V-0.
   HOOD: GLASS FILLED POLYESTER, UL 94V-0, COLOR - BLUE.
   CONTACTS ORDERED SEPARATELY.
2. ELECTRICAL CHARACTERISTICS:
   INSULATOR RESISTANCE: 5 G. OHMS PER IEC 512-2. TEST 3a, METHOD A.
   WORKING VOLTAGE: DESIGNED TO MEET UL 600 VAC AND CSA 600 VAC.
3. TEMPERATURE RANGE: -55°C TO 125°C.
4. DIMENSIONS ARE IN INCHES [MILLIMETERS].

POSITRONIC INDUSTRIES INC.
www.connectpositronic.com
FSCM 28198

DECIMAL TOL. ± 0.015 [0.38]
WF # 3989
ANGULAR TOL. ± N/A

POWER-LOK SERIES
SCALE N.T.S.
DRAWN BY M. ENEA
APPROVED BY

TITLE
PLA04F0050

DATE 9-6-01
DRAWING NUMBER SK2291
REV. A

Downloaded from Arrow.com.