




Copyright FCI.




spec ref		*		dr	Wei-Long Zhang	2010/11/01	projection	mm	size	A4	scale	1.000	
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Wei-Long Zhang	2011/04/28			ecn no				ELX-DG-003692-1
				chr	Max Xiu	2011/04/28			rel level				Released
				appr	Pei-Ming Zheng	2011/04/28			product family				
surface	linear	0.X	±0.50		title	PRESS FIT TYPE POWER EDGE CONNECTOR 25 X 2			dwg no	10075664-007		rev	C
		0.XX	±0.25										
		0.XXX	±0.05										
	angular	0°	±2°	www.fci.com	cat. no.	*	Product - Customer Drw			sheet 1 of 2			


PrintE File - REV C - 2009-06-09



Copyright FCI.



RECOMMENDED PCB LAYOUT
PCB THICKNESS: 3.18MM



CONNECTOR NOTE:
1. HOUSING MATERIAL: HIGH TEMPERATURE THERMOPLASTIC
UL 94V-0, FLAME RETARDANT
2. TERMINAL: COPPER ALLOY
3. PLATING:
Ni: 50u"/1.27um UNDER PLATED
Au: 30u"/0.76um ON CONTACT AREA (ONE SIDE)
Sn: 50u"/1.27um ON PRESS FIT TAIL
4. MANUFACTURING CODE PLEASE REFERENCE FCI
SPECIFICATION GS-24-007.

PCB NOTE:
5. ALL THROUGH HOLES ARE LOCATED WITH A TRUE POSITION OF 0.1mm.
6. ALL DIAMETERS ARE FINISHED HLD SIZES.
7. Ø1.15mm DRILLED HOLES, PLATED WITH 0.007mm MIN. HASL-FREE Pb.
OVER 1.03mm TO 0.08mm Cu PLATING TO ACHIEVE A 1.02±0.07mm HOLE.

spec ref *				dr Wei-Long Zhang		2010/11/01		projection		size A4		scale 1.000			
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng Wei-Long Zhang		2011/04/28						ecn no ELX-DG-003692-1			
				chr Max Xiu		2011/04/28									
				appr Pei-Ming Zheng		2011/04/28									
										product family				rel level Released	
surface		linear		0.X		±0.50				title PRESS FIT TYPE POWER EDGE CONNECTOR 25 X 2		dwg no 10075664-007		rev C	
				0.XX		±0.25									
				0.XXX		±0.05									
		angular		0°		±2°		www.fci.com		cat. no. *		Product - Customer Drw			

PrintE File - REV C - 2009-06-09